

[See all 13 Products in Family](#)

TECHSPEC[®]

T-Mount, 40mm Cube Mount, 1/4-20



12.5mm x 17.5mm Plate S-Mount Holder



Stock **#63-981** 1 In Stock

-

1

+

€484^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€484,00 each
Qty 5-9	€427,30 each
Qty 10-25	€393,40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

	Function:
Optic Mount (Fixed)	
	Type of Optics:
Cube	

Note: Includes four T-Mount Aperture Caps (#66-037)	
Dimensions of Compatible Optics (mm): 40.0 Sq.	
Physical & Mechanical Properties	
Dimensions (mm): 54.5 x 54.5 x 63.8	
Extension Length (mm): 54.5	
Min. Thickness of Compatible Optics (mm): 40.0	
Max. Thickness of Compatible Optics (mm): 40.0	
Threading & Mounting	
Thread Type: T-Mount	
Compatible Post: 1/4-20	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 235: Compliant	

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

