

[See all 13 Products in Family](#)

TECHSPEC® T-Mount, 60mm x 85mm Plate Mount, 1/4-20



Stock **#65-982** **1 In Stock**

- 1 + €530⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€530,00 each
Qty 5-9	€494,60 each
Qty 10-25	€470,20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Rectangular

Note:
Includes four T-Mount Aperture Caps ([#66-037](#))

Dimensions of Compatible Optics (mm):

Physical & Mechanical Properties

75.0 x 75.0 x 75.0 **Dimensions (mm):**

75.0 **Extension Length (mm):**

1.0 **Min. Thickness of Compatible Optics (mm):**

7.1 **Max. Thickness of Compatible Optics (mm):**

Threading & Mounting

T-Mount **Thread Type:**

1/4-20 **Compatible Post:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 233:**

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

