

[See all 3 Products in Family](#)

## TECHSPEC® T-Mount Iris Diaphragm Mount



T-Mount Iris Diaphragm Mount, #52-299

Stock **#52-299** **2 In Stock**

- 1 + €226<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€226,00 each
Qty 5-9	€199,40 each
Qty 10-25	€184,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Iris Diaphragm **Function:**

### Physical & Mechanical Properties

18.13 **Extension Length (mm):**

**Total Length (mm):**

22.0

1.2 - 30.0

Clear Aperture CA (mm):

58.0

Outer Diameter (mm):

### Threading & Mounting

T-Mount Thread Type:

### Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 219:

View Certificate of Conformance:

## Product Details

- Variable Apertures for C, S, and T-Mount Systems
- Male and Female Thread at Opposite Ends for Easy Integration
- Adjusted via Rotating Ring or Lever for Precision Control

TECHSPEC® C, S, and T-Mount Iris Diaphragm Mounts feature iris diaphragms that allow for precision control over the internal aperture within a system. Using male and female threads, these mounts can be placed anywhere within a C, S, or T-Mount system. The apertures can be adjusted via a rotating ring for the C-Mount version, with a 4mm lever for the S-Mount version and with a 5mm lever for the T-Mount version. TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts add 12mm, 12mm, and 18mm to the system length, respectively. These mounts are ideal for providing control over the *f*#, field stop diameter, and overall energy throughput of a C, S, or T-Mount system.

**NOTE:** The iris planes sit approximately 15mm, 8mm, and 12mm from the female ends of the TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts, respectively.

## Technical Information

