

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #26-397 [CONTACT US](#)



1



€8.109,00

ADD TO CART

Qty 1+

€8.109,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Polarization:
p

Dimensions (inches):
9 x 8 x 4

Wavelength Range (nm):
780 - 830

GDD Specification (fs²):
-10400 to -2600

Input Beam Diameter, 1/e² (mm):
2 (maximum)

Minimum Efficiency (%):

97.60

GDD Increment (fs²):

-2600

Regulatory Compliance

RoHS:

Compliant

Certificate of Conformance:

[View](#)