

TECHSPEC®

Two Knob Stage & 250mm Track Combination



One Knob Stage and Track Combination



Stock **#59-264** [CONTACT US](#)

- 1 +

€304,00

ADD TO CART

Qty 1+

€304,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Type of Drive:
Rack and Pinion

Type:
Metric

Stage Size (mm):

62 x 60
Travel (mm): 250
Construction: Black Anodized Aluminum
Graduation (mm): Track: 1 Vernier Reading: 0.1
Load Capacity, Normal (kg): 5
Load Capacity, Vertical (kg): 2
Mounting Threads: (1) M6 x 1, (8) M4 x 0.7 on Carrier
Note: Track & Two Knob Carrier Set
S.H.C.S. C'bore: (6) 6.5mm Thru on Track
Travel Per Knob Rotation (mm): 18
Straight Line Accuracy (mm): 0.1 - 0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
