

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® VIS (400-700nm) OD 4.0 25nm Bandpass Filter Kit, 25mm Dia



Stock #88-300 3-4 DAYS

- 1 + €1.230,00

ADD TO CART

Qty 1+
€1.230,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
25.00

Filters Included :
CWL: [400nm](#), [450nm](#), [500nm](#), [550nm](#), [600nm](#),
[650nm](#), [700nm](#)

Coating:

Hard Coated
Type: Bandpass Filter
Typical Applications: LED Cleanup, Bio-Imaging, Machine Vision
Wavelength: VIS
Number of Filters: 7
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.6

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View