

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® VIS Coated, C-Mounted Non-Polarizing Cube Beamsplitter



C-Mounted Cube Beamsplitters

Stock #49-682 3-4 DAYS



1



€396,00

ADD TO CART

Qty 1-4

€396,00

Qty 5+

€311,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (arcmin):
±2

Coating:
Faces: Multi-Layer Anti-Reflection for Visible Region

Construction:
Cube

Dimensions (mm): 38.0 x 38.0 x 50.0
Extension Length (mm): 38.0
Housing: Black Anodized Aluminum
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Thread Type: C-Mount (1" x 32 TPI)
Type: Non-Polarizing Beamsplitter
Type of Optics: Non-Polarizing Cube Beamsplitter, V/S Coating
Wavelength Range (nm): 430 - 670
Beamsplitter Included: #47-009

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View