

VZM™ 450i Zoom Imaging Lens



Stock **#54-671** CLEARANCE 3-4 DAYS

- 1 +

€751,95

ADD TO CART

Qty 1+

€751,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
239.00

Horizontal Field of View, 1/2" Sensor:
8.8 - 1.4mm

Horizontal Field of View, 2/3" Sensor:
12.0 - 1.9mm

Filter Thread:

M22.5 x 0.50
Maximum Diameter (mm): 35.00
Weight (g): 405.00
Working Distance Tolerance (mm): +3/-4
Resolution, Object Space: 30 - 144
Resolution, Image Space: 40 - 32
Zoom Ratio: 6.4:1
Type: Zoom Lens
Primary Magnification PMAG: 0.7X - 4.5X
Maximum Sensor Format: 2/3"
Working Distance (mm): 90.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View