

TECHSPEC® 125mm X-Y Positioning Stage



125mm X-Y Positioning Stage

Stock #12-694 **5 In Stock**

⊖ 1 ⊕ €620.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€620,00 each
Qty 5+	€547,70 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Universal **Type:**
Movement **Note:**

Physical & Mechanical Properties

Linear (X-Y) **Type of Movement:**

Ball Slide	Guide System:
Center Drive	Drive Orientation:
70 (±35mm) in X and Y	Travel (mm):
2.75 (±1.37) in X and Y	Travel (inches):
10	Load Capacity, Normal (kg):
60	Straight Line Accuracy (µm):
18	Travel Per Knob Rotation (mm):

Hardware & Interface Connectivity

Rack and Pinion	Type of Drive:
-----------------	-----------------------

Threading & Mounting

(4) M3 x 0.5	Mounting Threads:
--------------	--------------------------

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Compatible with Our [TECHSPEC® Manual Translation Stages](#) for Additional Axis Alignment
- ±12.5mm or ±35mm Travel in Both X and Y for Quick X-Y Positioning
- Universal Bottom Plate for Both [English and Metric Breadboard](#) Mounting

TECHSPEC® X-Y Positioning Stages feature a low profile design and two stacked rack and pinion movements to allow for travel in both X and Y axes. English or Metric top plates are sold separately from the rack and pinion mechanisms. TECHSPEC® X-Y Positioning Stages come in two sizes, a 46mm version with a 65mm footprint and a 125mm version with a 125mm footprint, to accommodate a range of benchtop translation applications. The English top plates are compatible with our TECHSPEC English Manual Translation Stages, while the Metric top plates are compatible with our TECHSPEC Metric Manual Translation Stages. The Rack & Pinion Drive Mechanisms come with a black anodized bottom plate featuring a universal hole pattern, which allows it to mount to both [English and Metric standard breadboards](#) directly without using additional adapter plates. TECHSPEC® X-Y Positioning Stages are ideal for quick X-Y positioning applications.

Technical Information

Use (4) M4 Socket Head Cap Screws included with #12-694 to assemble #12-694 together with either #12-692 or #12-693 to complete the X-Y Positioning Stage.

