

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #90-709 □ In Stock



1



€180,00

ADD TO CART

Qty 1+

€180,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Thickness (inches):
0.009

Thickness (mm):
0.24

Note:
Recommended Pulsed Width: 1ns to 30ms
Recommended Power Level Range: 5 mJ/cm² to 20 J/cm²

Sheet Size (in):
4 x 8

Sheet Size (mm):
101.6 x 203.2

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)