

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Zero Aperture, 25mm Max. Aperture, Mounted Iris Diapnragm



Stock #62-654 3-4 DAYS

-

1

+

 €92,00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €92,00                        |
| Qty 10+                       |
| €81,50                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Mounted

Minimum Aperture (mm):  
0.00

Maximum Aperture (mm):

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| 25.0                                                                                                |
| <b>Outer Diameter (mm):</b><br>52.0                                                                 |
| <b>Construction:</b><br>Black Anodized Aluminum, Black Spring Steel Leaves,<br>Stainless Steel Pins |
| <b>Lever Diameter (mm):</b><br>3.00                                                                 |
| <b>Lever Length (mm):</b><br>12.80                                                                  |
| <b>Number of Leaves:</b><br>Two Sets of 7                                                           |
| <b>Spacing of Leaf Layers (mm):</b><br>2.4                                                          |
| <b>Thickness (mm):</b><br>9.50                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Contains SVHC(s)</a>      |