In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® Calcium Fluoride (CaF2) Aspheric Lenses

Stock **#13-466** 3-4 DAYS

- 1 + **€504,00**

ADD TO CART

Qty 1-5
€504,00

Qty 6+
€453,60

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

CUSTOM OPTIONS

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
25.00 @ 4000nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm):
18.37

Substrate:
Calcium Fluoride (CaF_2) Vacuum UV Grade

Aspheric Design Wavelength (nm):
4000

Asphere Figure Error, RMS @ 632.8nm:
λ/6

Coating:
Uncoated

Centering (arcmin):
<1

Surface Quality:
60-40

Clear Aperture CA (mm):
22.50

Edge Thickness ET (mm):
2.59

Center Thickness CT (mm):
11.00 ±0.10

f/#:
1.00

Edges:
Diamond Turned

Type:
Aspheric Lens

Wavelength Range (nm):
200 - 7000

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
View