print-screen-header

SCHOTT NG11, 0.15 OD, 25mm Dia., Absorptive ND Filter

See More by SCHOTT Optical Components



Stock **#16-661** 3-4 DAYS

- 1 + **€42,00**

ADD TO CART

Qty 1-10
€42,00

Qty 11+
€37,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.15 ±0.006 @ 546nm

Glass/Filter Number:
SCHOTT NG11

Coating:
Uncoated

Index of Refraction n_d:
1.50

Surface Quality:
80-50

Transformation Temperature (°C):
481

Thickness (mm):
1.10

Thickness Tolerance (mm):
(nominal)

Transmission (%):
70.79 ±0.92% @ 546nm

Type:
Neutral Density Filter

Dimensional Tolerance (mm):
±0.38

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
View