print-screen-header

English EUR Contact Us

All Products / Lights and Illumination / Microscopy Lighting / Fiber Optic Light Guides / Semi-Rigid Light Guides

See all 4 Products in Family

23" Dual Branch Semi-Rigid Light Guide

Stock **#54-212** In Stock

- 1 + **€422,00**

ADD TO CART

Qty 1+

€422,00

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Acceptance Angle (°):
68.00

Minimum Bend Radius (mm):
101.6

Fiber Bundle Diameter (inches):
0.265

Length (inches):
23.00

Numerical Aperture NA:
0.55

Operating Temperature (°C):
-40 to +107

Fiber Diameter (µm):
50.00

Type:
Dual Branch

Length Tolerance (inches):
±0.5

Packing Fraction (%):
82.00

Index of Refraction n_d - Core:
1.581

Index of Refraction n_d - Cladding:
1.487

Transmission Loss:
6% per foot at 600nm

Type of Illumination:
Fiber Optic Light Guide

Compatible Light Guide Adapter:
SX: #38-947

Geometry:
Spot Light

Regulatory Compliance

Reach 174:
Compliant

RoHS:
Not Compliant

Certificate of Conformance:
View