In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Effilux High Power LED Backlights

Stock **#22-102** 3-4 DAYS

\- 1 + **€1.235,00**

ADD TO CART

Qty 1+
€1.235,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | Learn More

Get Product Downloads

Color:
Red

Operating Temperature (°C):
0 - 50

Dimensions (mm):

339 x 339

Wavelength (nm):
625.00

Weight (g):
3500

Power Supply:
Power Supply Required and Sold Separately:
USA: **#15-874**
Europe: **#15-875**
Japan: **#15-875**
Korea: Not Available
China: **#15-874**

Active Area (mm):
300 x 300

Type of Illumination:
LED illumination

Uniformity (%):
>90%

Manufacturer:
Effilux

Geometry:
Backlight

Illumination Mode:
Continous with AIC (Analog Intensity Control)

Regulatory Compliance

RoHS 2015:
Compliant

Reach 224:
Compliant

Certificate of Conformance:
View