In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT



Stock **#16-384** 3-4 DAYS

Additional Bandwidths

- 1 + **€47,00**

ADD TO CART

Qty 1-10
€47,00

Qty 11+
€41,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
514.00

Density (g/cm^3):
2.64

Glass/Filter Number:
SCHOTT BG55

Coating:
Uncoated

Color:
Blue-Green

Index of Refraction n_d:
1.54

Surface Quality:
60-40

Transformation Temperature (°C):
453

Thickness (mm):
2.00 ±0.2

Type:
Bandpass Filter

Wavelength:
UV-VIS

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
View