50 x 50mm 520nm, LED Backlight

See More by Advanced Illumination

Advanced Illumination High Intensity LED Backlights

Stock **#66-832** CONTACT US

- 1 + **€723,00**

ADD TO CART

Qty 1+

€723,00

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | Learn More

Get Product Downloads

Color:
Green

Model Number:
BL020201-520-IC

Operating Temperature (°C):
0 to 65

Dimensions (mm):
72 H x 72 W x 12 D

Wavelength (nm):
520.00

LED Lifetime (hours):
50,000

Wavelength Tolerance (nm):
±25

Power Supply:
Power Supply Required and Sold Separately:
USA: #66-855
Europe: #66-855
Japan: #66-855
Korea: #33-773
China: #66-855

Number of LEDs:
48.00

Number of Channels:
1.00

Type of Illumination:
LED Illuminator

Note:
Optional Manual Intensity Adjustment #86-887 and
#89-555 are Available

Uniformity (%):
±6 over Illuminated Area (Dependent on Working
Distance)

Manufacturer:
Advanced Illumination

Geometry:
Backlight

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 233:
Contains SVHC(s)