TECHSPEC® 30mm Diameter Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock **#83-364** 3-4 DAYS

- 1 + **€37,50**

ADD TO CART

Qty 1-5
€37,50

Qty 6+
€29,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):

8

Clear Aperture (%):
90.00

Clear Aperture CA (mm):
27.00

Diameter (mm):
30.00 ±0.13

Thickness (mm):
1.10 (nominal)

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10^{-6}/°C):
7.58 (0 to +300°C)

Density (g/cm^3):
2.39

Edges:
Fine Ground

Index of Refraction n_d:
1.5

Poisson's Ratio:
0.22

Substrate:
Gorilla® Glass

Surface Quality:
80-50

Type:
Protective Window

Wavelength Range (nm):
350 - 2200

Young's Modulus (GPa):
70

Regulatory Compliance

RoHS 2015:
Compliant

Reach 219:
Compliant

Certificate of Conformance:
View