Hoya B370 (UV-VIS) 25.4mm Dia., Colored Glass Bandpass Filter

See More by Hoya





+1

Stock **#48-634** 3-4 DAYS

Additional Bandwidths

- 1 + **€63,00**

ADD TO CART

Qty 1-10
€63,00

Qty 11+
€56,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Center Wavelength CWL (nm):
370.00

Density (g/cm^3):
2.36

Full Width-Half Max FWHM (nm):
100.00

Glass/Filter Number:
Hoya B370

Substrate:
Colored Glass

Coating:
Uncoated

Color:
Blue-Violet

Surface Quality:
60-40

Thickness (mm):
2.50

Thickness Tolerance (mm):
±0.2

Type:
Bandpass Filter

Wavelength:
UV-VIS

Parallelism (arcmin):
≤1

Dimensional Tolerance (mm):
+0/-0.25

Regulatory Compliance

RoHS 2015:
Exempt

Reach 224:
Compliant

Certificate of Conformance:
View