Edmund

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Mounted M46 x 0.75 - UV Cut-Off Filter

Mounted UV Filters

Stock **#54-041** 3-4 DAYS

- 1 + **€55,00**

ADD TO CART

Qty 1-9
€55,00

Qty 10+
€51,80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
41.0

Cut-On Wavelength (nm):
390.00

Filter Thread:
M46 x 0.75

Glass/Filter Number:
L-39

Substrate:
Hoya L-39

Operating Temperature (°C):
-15 to +70

Coating:
AR Coated

Color:
Clear

Outer Diameter (mm):
48.0

Thickness with Mount (mm):
4.50

Surface Quality:
80-50

Thickness (mm):
2.00

Thickness Tolerance (mm):
±0.2

Type:
Mounted Imaging Filter

Coating Specification:
R_{avg} >2% @ 400 - 700nm

Wavelength Range (nm):
350 - 2200

Surface Flatness (P-V):
4 - 6λ

Regulatory Compliance

RoHS:
Exempt

Certificate of Conformance:
View