See all 1 Products in Family

Sectional LED Ring Light, 220V

Stock **#68-770** **1 In Stock**

- 1 + **€260**.00

ADD TO CART

Volume Pricing	
Qty 1-5	**€260,00** each
Qty 6+	**€234,00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Number of LEDs:	72.00
Type of Illumination:	LED Illuminator
Note:	Power Supply Included

Requires 110V to 220V Inversion for Use in the US

Geometry:
Ring Light

Illumination Mode:
Constant

Physical & Mechanical Properties

Inner Diameter (mm):
60.5

Optical Properties

Color:
White

Hardware & Interface Connectivity

Operating Voltage (V):
220.00

Environmental & Durability Factors

Color Temperature (K):
6400.00

Regulatory Compliance

Certificate of Conformance:
View

PRODUCT DETAILS

- Large Inner Diameters for Easy Mounting
- 6400K Color Temperature
- Features Sectional Light Control

LED Ring Light Illuminators are strong alternatives to traditional fluorescent ring lights. The sectional ring light features lighting control in each of the unit's four quadrants, a 60.5mm inner diameter, and 72 LEDs. The sectional ring light is controlled using a panel on the top of the unit. LED Ring Light Illuminators are ideal for use with reflective parts and features a 70mm inner diameter and 60 LED bulbs. Sectional Light Control and Polarizer/Analyzer models are available.

Note: Due to CE restrictions, **#68-771** Polarizer/Analyzer LED Ring Light is not available in all regions. Please **contact us** for a suitable replacement.