

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

Standard Series Iris Diaphragms




- Used to Adjust f/#, Field Stop Diameter, and Overall Light Throughput
- Mounted Version Features a Tapped Hole for Post Mounting
- Abundant Types for Varying Applications


Technical Information

Types of Levers

Pin Lever



Tab Lever



Products

Type	Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Stock Number	Price	Buy
Unmounted	0.6	5.0	10.0	6.00	#54-352	€69,00 Qty 5+ €60,80	3-4 days
Unmounted	0.8	8.0	14.8	8.00	#32-623	€48,50 Qty 5+ €42,90	3-4 days
Unmounted	1.0	8.5	15.5	9.00	#42-124	€68,00 Qty 5+ €60,30	3-4 days
Unmounted	0.80	12.0	19.8	10.00	#30-263	€47,50 Qty 5+ €42,00	In Stock
Unmounted	1.0	14.0	22.0	10	#42-123	€68,00 Qty 5+ €60,30	3-4 days
Unmounted	1.2	15.0	24.0	12.00	#32-622	€47,50 Qty 5+ €42,00	3-4 days
Unmounted	1.2	18.0	28.0	12.00	#32-621	€68,00 Qty 5+ €60,30	3-4 days
Unmounted	1.2	20.0	30.0	12.00	#35-111	€51,50 Qty 5+ €45,60	In Stock
Unmounted	1.5	18.0	31.0	11	#36-623	€58,50 Qty 5+ €51,80	3-4 days
Unmounted	1.4	22.0	33.0	14.00	#32-620	€81,50 Qty 5+ €72,10	3-4 days
Unmounted	0.8	25.0	37.0	14.00	#35-110	€58,50 Qty 5+ €51,80	In Stock
Unmounted	1.5	28.0	40.0	16.00	#42-122	€92,50 Qty 5+ €82,00	In Stock
Unmounted	1.2	25.0	42.6	10	#40-997	€96,00 Qty 5+ €85,10	3-4 days
Unmounted	1.5	30.0	42.0	16.00	#64-500	€101,00 Qty 5+ €89,10	In Stock
Unmounted	1.2	30.0	48.0	12	#40-998	€101,00 Qty 5+ €89,10	3-4 days
Unmounted	1.2	30.0	48.5	10	#42-121	€92,50 Qty 5+ €82,00	3-4 days

Unmounted	1.5	34.0	49.0	14.00	#41-972	€101,00 Qty 5+ €89,10	In Stock
Unmounted	1.9	36.0	50.0	16.00	#32-619	€77,50 Qty 5+ €68,50	3-4 days
Unmounted	1.9	37.0	53.0	16.00	#32-618	€85,50 Qty 5+ €75,70	3-4 days
Unmounted	2	41.0	55.0	18	#41-973	€101,00 Qty 5+ €89,10	3-4 days
Unmounted	2	42.0	58.0	18.00	#30-118	€96,00 Qty 5+ €85,10	3-4 days
Unmounted	2.5	40.0	60.0	12.00	#36-624	€122,00 Qty 5+ €108,00	3-4 days
Unmounted	2.5	50.0	70.0	16.00	#32-617	€139,00 Qty 5+ €123,20	3-4 days
Unmounted	7.0	59.0	77.0	20.00	#32-616	€195,00 Qty 5+ €172,70	3-4 days
Unmounted	3.0	58.0	80.0	18.00	#32-615	€195,00 Qty 5+ €172,70	3-4 days
Unmounted	4.0	60.0	82.0	17	#36-625	€203,00 Qty 5+ €178,90	In Stock
Unmounted	4.5	70.0	92.0	20.00	#32-614	€268,00 Qty 5+ €236,40	3-4 days
Unmounted	4.5	75.0	100.0	20.00	#30-264	€302,00 Qty 5+ €267,00	In Stock
Unmounted	4.5	80.5	110.0	16.00	#32-613	€330,00 Qty 5+ €291,20	3-4 days
Unmounted	5.0	90.0	120.0	20.00	#32-612	€382,00 Qty 5+ €337,00	3-4 days
Unmounted	5.0	98.0	130.0	20.00	#32-611	€409,00 Qty 5+ €361,20	3-4 days
Unmounted	5.0	104.0	140.0	16.00	#32-610	€439,00 Qty 5+ €387,30	3-4 days
Unmounted	6.0	110.0	150.0	20.00	#60-644	€475,00 Qty 5+ €419,70	3-4 days
Unmounted	6.0	120.0	165.0	18.00	#32-609	€494,00 Qty 5+ €435,80	3-4 days
Unmounted	11.5	138.0	180.0	20.00	#32-608	€640,00 Qty 5+ €564,20	In Stock

Unmounted	11.0	158.0	208.0	20.00	#70-894	€775,00 Qty 5+ €681,70	3-4 days
Unmounted	12.0	225.0	300.0	18.00	#70-895	€795,00 Qty 5+ €702,80	3-4 days
Mounted	0.6	5.0	26.5	6.00	#23-242	€88,50 Qty 5+ €78,00	3-4 days
Mounted	0.8	8.0	26.5	8.00	#23-243	€71,00 Qty 5+ €62,60	Contact Us
Mounted	0.80	12.0	39.0	10.00	#23-244	€69,00 Qty 5+ €60,80	3-4 days
Mounted	1.0	14.0	39.0	10.00	#23-245	€84,50 Qty 5+ €74,50	3-4 days
Mounted	1.2	15.0	39.0	12.00	#23-246	€71,00 Qty 5+ €62,60	3-4 days
Mounted	1.2	18.0	52.0	12.00	#23-247	€84,50 Qty 5+ €74,50	3-4 days
Mounted	1.2	20.0	52.0	12.00	#23-248	€76,00 Qty 5+ €67,00	3-4 days
Mounted	0.8	12.0	30.8	-	#53-914	€62,00 Qty 5+ €54,90	3-4 days
Mounted	1.4	22.0	52.0	14.00	#23-249	€98,00 Qty 5+ €86,30	3-4 days
Mounted	0.8	25.0	52.0	14.00	#23-250	€79,50 Qty 5+ €70,10	3-4 days
Mounted	1.5	28.0	78.0	16.00	#23-251	€108,00 Qty 5+ €95,10	3-4 days
Mounted	1.9	37.0	78.0	16.00	#23-252	€102,00 Qty 5+ €89,90	3-4 days
Mounted	0.8	25.0	50.8	-	#53-915	€74,00 Qty 5+ €65,30	3-4 days
Mounted	1.50	37.0	66.0	-	#53-916	€92,50 Qty 5+ €82,00	3-4 days
Mounted	2.5	50.0	90.0	16.00	#23-253	€147,00 Qty 5+ €129,50	3-4 days
Mounted	2.50	50.0	86.0	-	#53-917	€158,00 Qty 5+ €139,40	3-4 days
Mounted	11.5	138.0	205.0	20.00	#23-254	€660,00 Qty 5+ €580,90	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com