


[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Float Glass](#)

Visible Laser Diode Mirrors



- Over 95% Reflectance of Visible Laser Diode Light
- Ideal for Multiple Reflection Systems
- Coating Optimized for 633nm at 45° AOI

Common Specifications

Physical & Mechanical Properties

Dimensional Tolerance (mm):	±0.25
-----------------------------	-------


Optical Properties

Substrate:	Float Glass		
Surface Quality:	80-50	Coating Specification:	R _{abs} >97% @ 633nm
Coating:	Dielectric Mirror (500-700nm)	Coating Type:	Dielectric
Design Wavelength DWL (nm):	633		

Environmental & Durability Factors

Durability:	MIL-C-48497A
-------------	--------------

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Coating Specification	Stock Number	Price	Buy
5.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#46-617	€26,27 Volume Pricing	10 In Stock
10.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#43-853	€26,27 Volume Pricing	20+ In Stock
12.50	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#46-618	€26,27 Volume Pricing	20+ In Stock
15.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#43-854	€26,27 Volume Pricing	20+ In Stock
20.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#46-619	€26,27 Volume Pricing	Contact Us
25.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#43-532	€28,33 Volume Pricing	5 In Stock
-	32.0 x 32.0	6.35	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#31-495	€28,33 Volume Pricing	20+ In Stock
-	47.0 x 51.0	6.35	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#31-496	€40,17 Volume Pricing	15 In Stock
50.00	-	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#43-855	€40,17 Volume Pricing	20+ In Stock
-	50.0 x 50.0	3.00	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#43-533	€40,17 Volume Pricing	8 In Stock
-	64.0 x 97.0	6.35	Dielectric Mirror (500- 700nm)	R _{abs} >97% @ 633nm	#31-497	€48,93 Volume Pricing	5 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com