


[All Products](#) /
 [Optics](#) /
 [Optical Mirrors](#) /
 [Flat Mirrors](#) /
 [Laser Mirrors](#)

TECHSPEC® Precision Broadband Laser Mirrors



- Ideal for Tunable Lasers and Reflecting Multiple Laser Sources
- High Reflectivity from 0 - 45° for All Polarization States
- Variety of Coating Options Available

Common Specifications

General

Note:

Optical Power: $\lambda/10$

Physical & Mechanical Properties

Back Surface:

Ground



Optical Properties

Surface Quality: 20-10


Irregularity (P-V) @
632.8nm: $\lambda/20$

Angle of Incidence (°): 0-45


Technical Information



Mirror for UV 300-500nm



Mirror for Near-IR



Products

Wavelength Range (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
300 - 550	12.70	5.00	0-45	#48-015	€133,90 Volume Pricing	5 In Stock
300 - 550	25.40	8.00	0-45	#48-016	€165,83 Volume Pricing	7 In Stock
400 - 700	12.70	5.00	0-45	#45-754	€133,90 Volume Pricing	20+ In Stock
400 - 700	25.40	8.00	0-45	#45-596	€165,83 Volume Pricing	Contact Us
#75-420 New						
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!						
400 - 700	50.80	12.50	0-45		€334,75	9 In Stock
700 - 900	12.70	5.00	0-45	#45-755	€133,90 Volume Pricing	20+ In Stock
700 - 900	25.40	8.00	0-45	#45-597	€165,83 Volume Pricing	20+ In Stock

[#75-421 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

700 - 900	50.80	12.50	0-45	€334,75	8 In Stock
-----------	-------	-------	------	---------	------------

450 - 12000	12.70	5.00	0-45	#45-757	€133,90 Volume Pricing	20+ In Stock
-------------	-------	------	------	-------------------------	---	--------------

450 - 12000	25.40	8.00	0-45	#45-758	€165,83 Volume Pricing	12 In Stock
-------------	-------	------	------	-------------------------	---	-------------

450 - 12000	50.80	12.50	0-45	#48-017	€394,49 Volume Pricing	20+ In Stock
-------------	-------	-------	------	-------------------------	---	--------------



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
Phone: 1-800-363-1992 :
www.edmundoptics.com