

[All Products](#) / [Optics](#) / [Prisms](#) / [Retroreflection Prisms](#)

Hollow Retroreflectors



- Incident Light is Reflected Back to the Source
- Hollow Lightweight Design
- No Material Absorption or Chromatic Aberration

Common Specifications

Dimensional Tolerance (mm): ± 1.6

Substrate: [BOROFLOAT®](#)

Surface Quality: 80-50

Image Orientation: Left-Handed

Ray Deviation (°): 180

Technical Information

Products

CA (mm)	Beam Deviation (arcsec)	Coating	Stock Number	Price	Buy
6.4	20.00	Enhanced Aluminum (450-650nm)	#46-169	€1.495,00 Volume Pricing	2 In Stock
6.4	20.00	Protected Gold (700-2000nm)	#46-180	€1.540,00 Volume Pricing	3 In Stock
12.7	5.00	Enhanced Aluminum (450-650nm)	#46-170	€1.550,00 Volume Pricing	1 In Stock
12.7	5.00	Protected Gold (700-2000nm)	#46-181	€1.595,00 Volume Pricing	1 In Stock
25.4	1.00	Enhanced Aluminum (450-650nm)	#46-172	€1.550,00 Volume Pricing	1 In Stock
25.4	1.00	Protected Gold (700-2000nm)	#46-183	€1.595,00 Volume Pricing	3 In Stock
25.4	1.00	Protected Silver (450-10000nm)	#70-688	€1.575,00 Volume Pricing	Contact Us
25.4	2.00	Enhanced Aluminum (450-650nm)	#46-173	€1.185,00 Volume Pricing	5 In Stock
25.4	2.00	Protected Gold (700-2000nm)	#46-184	€1.220,00 Volume Pricing	1 In Stock
25.4	5.00	Enhanced Aluminum (450-650nm)	#46-174	€880,00 Volume Pricing	1 In Stock

25.4	5.00	Protected Gold (700-2000nm)	#46-185	€905,00 Volume Pricing	1 In Stock
25.4	5.00	Protected Silver (450-10000nm)	#70-689	€890,00 Volume Pricing	5 In Stock
25.4	30.00	Enhanced Aluminum (450-650nm)	#46-175	€720,00 Volume Pricing	1 In Stock
25.4	30.00	Protected Gold (700-2000nm)	#46-186	€740,00 Volume Pricing	1 In Stock
50.8	1.00	Enhanced Aluminum (450-650nm)	#49-666	€1.910,00 Volume Pricing	1 In Stock
50.8	1.00	Protected Gold (700-2000nm)	#49-674	€1.965,00 Volume Pricing	4 In Stock
50.8	1.00	Protected Silver (450-10000nm)	#70-690	€1.935,00 Volume Pricing	Contact Us
50.8	2.00	Enhanced Aluminum (450-650nm)	#49-667	€1.565,00 Volume Pricing	1 In Stock
50.8	2.00	Protected Gold (700-2000nm)	#49-675	€1.610,00 Volume Pricing	3 In Stock
50.8	5.00	Enhanced Aluminum (450-650nm)	#49-668	€1.205,00 Volume Pricing	2 In Stock
50.8	5.00	Protected Gold (700-2000nm)	#49-676	€1.240,00 Volume Pricing	2 In Stock
50.8	5.00	Protected Silver (450-10000nm)	#70-691	€1.225,00 Volume Pricing	1 In Stock

50.8	30.00	Enhanced Aluminum (450-650nm)	#49-669	€915,00 Volume Pricing	6 In Stock
50.8	30.00	Protected Gold (700-2000nm)	#49-677	€940,00 Volume Pricing	2 In Stock
63.5	1.00	Enhanced Aluminum (450-650nm)	#46-176	€2.010,00 Volume Pricing	1 In Stock
63.5	1.00	Protected Gold (700-2000nm)	#46-187	€2.070,00 Volume Pricing	2 In Stock
63.5	1.00	Protected Silver (450-10000nm)	#70-692	€2.040,00 Volume Pricing	2 In Stock
63.5	2.00	Enhanced Aluminum (450-650nm)	#46-177	€1.655,00 Volume Pricing	1 In Stock
63.5	2.00	Protected Gold (700-2000nm)	#46-188	€1.705,00 Volume Pricing	1 In Stock
63.5	5.00	Enhanced Aluminum (450-650nm)	#46-178	€1.390,00 Volume Pricing	1 In Stock
63.5	5.00	Protected Gold (700-2000nm)	#46-189	€1.430,00 Volume Pricing	6 In Stock
63.5	5.00	Protected Silver (450-10000nm)	#70-693	€1.410,00 Volume Pricing	Contact Us

[#46-179 Clearance](#)



Clearance

63.5	30.00	Enhanced Aluminum (450-650nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€1.090,00 Volume Pricing	1 In Stock
63.5	30.00	Protected Gold (700-2000nm)	#46-190	€1.125,00 Volume Pricing	1 In Stock
127.0	1.00	Enhanced Aluminum (450-650nm)	#49-670	€11.750,00 Volume Pricing	Contact Us
127.0	1.00	Protected Gold (700-2000nm)	#49-678	€12.100,00 Volume Pricing	Contact Us
127.0	1.00	Protected Silver (450-10000nm)	#70-694	€11.930,00 Volume Pricing	1 In Stock
127.0	5.00	Enhanced Aluminum (450-650nm)	#49-672	€4.595,00 Volume Pricing	Contact Us
127.0	5.00	Protected Gold (700-2000nm)	#49-680	€4.735,00 Volume Pricing	3 In Stock
127.0	5.00	Protected Silver (450-10000nm)	#70-695	€4.665,00 Volume Pricing	Contact Us
127.0	30.00	Protected Gold (700-2000nm)	#49-681	€3.235,00 Volume Pricing	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com