

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

Zero Aperture Series Iris Diaphragms



- Provide Total Light Extinction When Closed
- Aperture Sizes Up to 75mm
- Mounted Options Available

Common Specifications

Physical & Mechanical Properties

Construction: Black Anodized Aluminum,
Black Spring Steel Leaves,
Stainless Steel Pins

Lever Diameter (mm): 3.00

Optical Properties

Minimum Aperture (mm): 0.00

Technical Information

Products

Type	Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Stock Number	Price	Buy
Unmounted	0.00	12.0	21.0	Two Sets of 5	#53-906	€53,05 Volume Pricing	20+ In Stock
Unmounted	0.00	18.0	29.0	Two Sets of 6	#62-649	€72,10 Volume Pricing	7 In Stock
Unmounted	0.00	25.0	38.0	Two Sets of 7	#53-907	€64,89 Volume Pricing	20+ In Stock
Unmounted	0.00	37.0	54.0	Two Sets of 8	#53-908	€84,98 Volume Pricing	6 In Stock
Unmounted	0.00	50.0	72.0	Two Sets of 8	#53-909	€152,44 Volume Pricing	5 In Stock
Unmounted	0.00	75.0	102.0	Two Sets of 10	#64-506	€221,45 Volume Pricing	2 In Stock
Mounted	0.00	12.0	39.0	Two Sets of 5	#23-278	€79,83 Volume Pricing	1 In Stock
Mounted	0.00	12.0	32.0	Two Sets of 5	#62-653	€80,86 Volume Pricing	3 In Stock
Mounted	0.00	25.0	52.0	Two Sets of 7	#23-279	€89,10 Volume Pricing	3 In Stock
Mounted	0.00	25.0	52.0	Two Sets of 7	#62-654	€97,85 Volume Pricing	5 In Stock
Mounted	0.00	37.0	78.0	Two Sets of 8	#23-280	€97,85 Volume Pricing	4 In Stock
Mounted	0.00	37.0	67.0	Two Sets of 8	#62-655	€116,39 Volume Pricing	2 In Stock
Mounted	0.00	50.0	88.0	Two Sets of 8	#62-656	€216,30 Volume Pricing	Contact Us



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com