

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Convex \(DCX\) Lenses](#)

TECHSPEC® VIS-NIR Coated Double-Convex (DCX) Lenses



- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- Minimize Aberrations Including Spherical and Coma
- [UV Fused Silica DCX Lenses](#) Available
- Other Coating Options Available: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

Common Specifications

Physical & Mechanical Properties

Bevel:

Protective bevel as needed

Optical Properties

Coating:

VIS-NIR (400-1000nm)

Coating Specification:

 $R_{\text{abs}} \leq 0.25\% \text{ @ } 880\text{nm}$
 $R_{\text{avg}} \leq 1.25\% \text{ @ } 400 - 870 \text{ nm}$
 $R_{\text{avg}} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$

 Focal Length Tolerance
 (%):

 ± 1

 Wavelength Range
 (nm):



400 - 1000

Technical Information

VIS-NIR Coating

$R_{avg} \leq 0.25\%$ @ 880nm, $R_{avg} \leq 1.25\%$ @ 400 - 1000nm

Typ. Energy Density Limit: 5 J/cm² @ 532nm, 10ns



Products

Dia. (mm)	BFL (mm)	EFL (mm)	Coating	Substrate	Stock Number	Price	Buy
3.00	2.21	3.00	VIS-NIR (400-1000nm)	N-SF5	#49-447	€67,00 Qty 10+ €60,50	3-4 days
3.00	3.78	4.50	VIS-NIR (400-1000nm)	N-BK7	#49-448	€67,00 Qty 10+ €60,50	3-4 days
3.00	5.37	6.00	VIS-NIR (400-1000nm)	N-BK7	#49-449	€67,00 Qty 10+ €60,50	3-4 days
3.00	8.46	9.00	VIS-NIR (400-1000nm)	N-BK7	#49-450	€67,00 Qty 10+ €60,50	3-4 days
4.50	3.70	4.50	VIS-NIR (400-1000nm)	N-LASF44	#47-893	€67,00 Qty 10+ €60,50	3-4 days
4.50	8.16	9.00	VIS-NIR (400-1000nm)	N-BK7	#47-894	€67,00 Qty 10+ €60,50	3-4 days
5.00	4.19	5.00	VIS-NIR (400-1000nm)	N-SF5	#63-658	€54,00 Qty 10+ €48,50	3-4 days
5.00	9.31	10.00	VIS-NIR (400-1000nm)	N-BK7	#63-659	€54,00 Qty 10+ €48,50	3-4 days
5.00	14.33	15.00	VIS-NIR (400-1000nm)	N-BK7	#63-660	€54,00 Qty 10+ €48,50	3-4 days
5.00	19.50	20.00	VIS-NIR (400-1000nm)	N-BK7	#63-661	€54,00 Qty 10+ €48,50	Contact Us
5.00	24.50	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-662	€54,00 Qty 10+ €48,50	3-4 days
6.00	5.19	6.00	VIS-NIR (400-1000nm)	N-SF5	#45-859	€43,50 Qty 10+ €39,00	3-4 days

6.00	8.22	9.00	VIS-NIR (400-1000nm)	N-BK7	#45-860	€43,50 Qty 10+ €39,00	3-4 days
6.00	11.18	12.00	VIS-NIR (400-1000nm)	N-BK7	#45-861	€43,50 Qty 10+ €39,00	3-4 days
6.00	17.26	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-862	€43,50 Qty 10+ €39,00	Contact Us
6.00	23.13	24.00	VIS-NIR (400-1000nm)	N-BK7	#45-863	€43,50 Qty 10+ €39,00	3-4 days
6.00	29.23	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-864	€43,50 Qty 10+ €39,00	3-4 days
6.00	35.33	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-865	€43,50 Qty 10+ €39,00	3-4 days
9.00	7.90	9.00	VIS-NIR (400-1000nm)	N-SF5	#45-866	€44,50 Qty 10+ €40,00	3-4 days
9.00	12.56	13.50	VIS-NIR (400-1000nm)	N-BK7	#45-867	€44,50 Qty 10+ €40,00	3-4 days
9.00	17.12	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-868	€44,50 Qty 10+ €40,00	3-4 days
9.00	26.08	27.00	VIS-NIR (400-1000nm)	N-BK7	#45-869	€44,50 Qty 10+ €40,00	3-4 days
9.00	35.15	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-870	€44,50 Qty 10+ €40,00	3-4 days
9.00	44.17	45.00	VIS-NIR (400-1000nm)	N-BK7	#45-871	€44,50 Qty 10+ €40,00	3-4 days
10.00	8.89	10.00	VIS-NIR (400-1000nm)	N-SF5	#63-663	€44,50 Qty 10+ €40,00	In Stock
10.00	13.80	15.00	VIS-NIR (400-1000nm)	N-BK7	#63-664	€44,50 Qty 10+ €40,00	3-4 days

10.00	19.16	20.00	VIS-NIR (400-1000nm)	N-BK7	#63-665	€44,50 Qty 10+ €40,00	In Stock
10.00	24.16	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-666	€44,50 Qty 10+ €40,00	3-4 days
10.00	29.17	30.00	VIS-NIR (400-1000nm)	N-BK7	#63-667	€44,50 Qty 10+ €40,00	3-4 days
10.00	39.16	40.00	VIS-NIR (400-1000nm)	N-BK7	#63-668	€44,50 Qty 10+ €40,00	3-4 days
10.00	49.17	50.00	VIS-NIR (400-1000nm)	N-BK7	#63-669	€44,50 Qty 10+ €40,00	3-4 days
10.00	99.17	100.00	VIS-NIR (400-1000nm)	N-BK7	#63-670	€44,50 Qty 10+ €40,00	3-4 days
12.00	10.79	12.00	VIS-NIR (400-1000nm)	N-SF5	#45-872	€47,50 Qty 10+ €42,75	3-4 days
12.00	16.81	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-873	€46,50 Qty 10+ €41,75	3-4 days
12.00	22.65	24.00	VIS-NIR (400-1000nm)	N-BK7	#33-391	€46,50 Qty 10+ €41,75	3-4 days
12.00	28.75	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-875	€46,50 Qty 10+ €41,75	3-4 days
12.00	34.90	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-876	€46,50 Qty 10+ €41,75	3-4 days
12.00	47.09	48.00	VIS-NIR (400-1000nm)	N-BK7	#45-877	€46,50 Qty 10+ €41,75	3-4 days
12.00	71.07	72.00	VIS-NIR (400-1000nm)	N-BK7	#45-878	€46,50 Qty 10+ €41,75	3-4 days
15.00	13.68	15.00	VIS-NIR (400-1000nm)	N-SF11	#45-879	€47,50 Qty 10+ €42,75	In Stock

15.00	18.99	20.00	VIS-NIR (400-1000nm)	N-SF11	#63-671	€46,50 Qty 10+ €41,75	3-4 days
15.00	21.29	22.50	VIS-NIR (400-1000nm)	N-SF11	#45-880	€46,50 Qty 10+ €41,75	3-4 days
15.00	23.82	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-672	€46,50 Qty 10+ €41,75	In Stock
15.00	28.82	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-881	€46,50 Qty 10+ €41,75	3-4 days
15.00	44.00	45.00	VIS-NIR (400-1000nm)	N-BK7	#63-673	€46,50 Qty 10+ €41,75	3-4 days
15.00	49.00	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-882	€46,50 Qty 10+ €41,75	3-4 days
15.00	59.00	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-674	€46,50 Qty 10+ €41,75	3-4 days
18.00	16.69	18.00	VIS-NIR (400-1000nm)	N-SF11	#63-675	€48,50 Qty 10+ €43,50	3-4 days
18.00	25.25	27.00	VIS-NIR (400-1000nm)	N-BK7	#45-883	€48,50 Qty 10+ €43,50	In Stock
18.00	34.59	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-884	€48,50 Qty 10+ €43,50	3-4 days
20.00	18.55	20.00	VIS-NIR (400-1000nm)	N-SF11	#63-678	€49,25 Qty 10+ €44,25	3-4 days
20.00	23.86	25.00	VIS-NIR (400-1000nm)	N-SF11	#63-679	€49,25 Qty 10+ €44,25	3-4 days
20.00	28.20	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-885	€49,25 Qty 10+ €44,25	3-4 days
20.00	38.44	40.00	VIS-NIR (400-1000nm)	N-BK7	#45-886	€49,25 Qty 10+ €44,25	In Stock

20.00	48.84	50.00	VIS-NIR (400-1000nm)	N-BK7	#63-680	€49,25 Qty 10+ €44,25	3-4 days
20.00	58.67	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-681	€49,25 Qty 10+ €44,25	3-4 days
20.00	78.67	80.00	VIS-NIR (400-1000nm)	N-BK7	#63-682	€49,25 Qty 10+ €44,25	3-4 days
25.00	22.47	25.00	VIS-NIR (400-1000nm)	N-SF5	#45-887	€52,00 Qty 10+ €46,75	3-4 days
25.00	28.31	30.00	VIS-NIR (400-1000nm)	N-SF5	#63-683	€51,50 Qty 10+ €46,25	3-4 days
25.00	32.81	35.00	VIS-NIR (400-1000nm)	N-BK7	#45-888	€51,50 Qty 10+ €46,25	3-4 days
25.00	38.21	40.00	VIS-NIR (400-1000nm)	N-BK7	#45-889	€51,50 Qty 10+ €46,25	3-4 days
25.00	48.29	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-890	€51,50 Qty 10+ €46,25	3-4 days
25.00	73.84	75.00	VIS-NIR (400-1000nm)	N-BK7	#45-891	€51,50 Qty 10+ €46,25	3-4 days
25.00	98.95	100.00	VIS-NIR (400-1000nm)	N-BK7	#45-892	€51,50 Qty 10+ €46,25	3-4 days
25.00	123.84	125.00	VIS-NIR (400-1000nm)	N-BK7	#45-893	€51,50 Qty 10+ €46,25	3-4 days
25.00	148.88	150.00	VIS-NIR (400-1000nm)	N-BK7	#45-894	€51,50 Qty 10+ €46,25	Contact Us
25.00	173.94	175.00	VIS-NIR (400-1000nm)	N-BK7	#45-895	€51,50 Qty 10+ €46,25	3-4 days
25.00	198.35	200.00	VIS-NIR (400-1000nm)	N-BK7	#33-397	€51,50 Qty 10+ €46,25	Contact Us

30.00	28.12	30.00	VIS-NIR (400-1000nm)	N-SF11	#63-684	€61,00 Qty 10+ €55,00	In Stock
30.00	47.82	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-898	€60,00 Qty 10+ €54,00	Contact Us
30.00	58.33	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-685	€60,00 Qty 10+ €54,00	3-4 days
30.00	73.35	75.00	VIS-NIR (400-1000nm)	N-BK7	#45-899	€60,00 Qty 10+ €54,00	3-4 days
30.00	98.34	100.00	VIS-NIR (400-1000nm)	N-BK7	#63-686	€60,00 Qty 10+ €54,00	In Stock
30.00	118.34	120.00	VIS-NIR (400-1000nm)	N-BK7	#63-687	€60,00 Qty 10+ €54,00	Contact Us
40.00	37.54	40.00	VIS-NIR (400-1000nm)	N-SF11	#63-688	€72,00 Qty 10+ €65,00	3-4 days
40.00	57.10	60.00	VIS-NIR (400-1000nm)	N-BK7	#45-900	€72,00 Qty 10+ €65,00	3-4 days
40.00	77.32	80.00	VIS-NIR (400-1000nm)	N-BK7	#33-422	€72,00 Qty 10+ €65,00	3-4 days
40.00	97.33	100.00	VIS-NIR (400-1000nm)	N-BK7	#33-409	€72,00 Qty 10+ €65,00	3-4 days
40.00	117.67	120.00	VIS-NIR (400-1000nm)	N-BK7	#63-689	€72,00 Qty 10+ €65,00	3-4 days
40.00	197.35	200.00	VIS-NIR (400-1000nm)	N-BK7	#33-416	€72,00 Qty 10+ €65,00	3-4 days
50.00	45.30	50.00	VIS-NIR (400-1000nm)	N-SF11	#45-905	€74,50 Qty 10+ €67,00	3-4 days
50.00	96.65	100.00	VIS-NIR (400-1000nm)	N-BK7	#45-906	€74,50 Qty 10+ €67,00	3-4 days

50.00	147.00	150.00	VIS-NIR (400-1000nm)	N-BK7	#45-907	€74,50 Qty 10+ €67,00	3-4 days
50.00	198.33	200.00	VIS-NIR (400-1000nm)	N-BK7	#45-908	€74,50 Qty 10+ €67,00	3-4 days
50.00	248.37	250.00	VIS-NIR (400-1000nm)	N-BK7	#45-909	€74,50 Qty 10+ €67,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com