

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#)

Norland Optical Adhesives

See More by [Norland](#)



- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Technical Information

Products

Norland Number	Size (oz)	Bonding Type	Glass Bonding	Metal Bonding	Index of Refraction (n _d)	Stock Number	Price	Buy
61	16	Glass to Glass/Metal	Excellent	Excellent	1.56	#15-697	€318,00 Qty 5+ €302,30	In Stock
63	16	Glass to Glass	Good	Good	1.56	#16-778	€318,00 Qty 5+ €302,30	3-4 days
65	16	Glass to Glass/Metal	Good	Good	1.52	#16-779	€318,00 Qty 5+ €302,30	3-4 days
68	16	Plastic to Plastic/Glass	Excellent	Good	1.54	#16-780	€318,00 Qty 5+ €302,30	3-4 days
81	16	Glass to Glass/Metal	Excellent	Excellent	1.56	#16-781	€318,00 Qty 5+ €302,30	3-4 days
60	1	Glass to Glass	Good	Good	1.56	#42-192	€38,75 Qty 5+ €36,60	In Stock
61	1	Glass to Glass/Metal	Excellent	Excellent	1.56	#37-322	€40,75 Qty 5+ €38,60	In Stock
63	1	Glass to Glass	Good	Good	1.56	#36-425	€40,75 Qty 5+ €38,60	In Stock
65	1	Glass to Glass/Metal	Good	Good	1.52	#36-426	€40,75 Qty 5+ €38,60	Contact Us
68	1	Plastic to Plastic/Glass	Excellent	Good	1.54	#36-427	€40,75 Qty 5+ €38,60	In Stock
68T	1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-392	€42,25 Qty 5+ €40,00	Contact Us
68TH	1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-791	€88,50 Qty 5+ €84,50	Contact Us
72	3.52	Plastic to Plastic/Glass	Excellent	Good	1.56	#17-344	€121,00 Qty 5+ €115,30	3-4 days
73	3.52	Glass to Glass	Excellent	Good	1.56	#17-345	€121,00 Qty 5+ €115,30	3-4 days
74	3.52	Plastic to Plastic/Glass	Excellent	Good	1.52	#17-346	€121,00 Qty 5+ €115,30	3-4 days
76	3.52	Glass to Plastic	Excellent	Good	1.51	#17-347	€121,00 Qty 5+ €115,30	3-4 days
78	3.52	Plastic to Plastic/Glass	Excellent	Good	1.50	#17-348	€121,00 Qty 5+ €115,30	3-4 days

81	1	Glass to Glass/Metal	Excellent	Excellent	1.56	#36-428	€40,75 Qty 5+ €38,60	In Stock
83H	1	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-583	€88,50 Qty 5+ €84,50	In Stock
85	1	Plastic to Plastic/Glass	Excellent	Fair	1.46	#88-140	€88,50 Qty 5+ €84,50	In Stock
86H	1	Glass to Glass/Plastic	Excellent	Good	1.55	#12-848	€88,50 Qty 5+ €84,50	Contact Us
86TH	1	Glass to Glass/Plastic	Excellent	Good	1.54	#17-349	€88,50 Qty 5+ €83,90	Contact Us
86TLH	1	Glass to Glass/Metal	Excellent	Excellent	1.55	#14-797	€88,50 Qty 5+ €84,50	Contact Us
87	1	Glass to Glass/Plastic	Excellent	Good	1.52	#17-350	€88,50 Qty 5+ €83,90	3-4 days
88	1	Glass to Glass/Metal	Excellent	Excellent	1.56	#14-841	€88,50 Qty 5+ €84,50	In Stock
89H	1	Glass to Glass	Excellent	Good	1.51	#17-351	€88,50 Qty 5+ €83,90	3-4 days
UVS 91	1	Liquid Crystal Displays	Excellent	Good	N/A	#17-364	€62,00 Qty 5+ €59,20	3-4 days
107	4	Glass to Metal	Excellent	Excellent	1.51	#62-048	€94,50 Qty 5+ €91,70	3-4 days
108H	3.52	Glass to Metal	Excellent	Excellent	1.51	#17-363	€106,00 Qty 5+ €100,20	Contact Us
139	1	Glass to Glass	Excellent	Good	1.39	#15-696	€174,00 Qty 5+ €168,20	3-4 days
144	1	Glass to Glass	Excellent	Good	1.44	#17-358	€118,00 Qty 5+ €112,20	3-4 days
146H	1	Plastic to Plastic/Glass	Excellent	Good	1.46	#12-866	€88,50 Qty 5+ €84,50	3-4 days
148	1	Glass to Glass	Excellent	Good	1.48	#17-359	€88,50 Qty 5+ €83,90	Contact Us
160	1	Glass to Glass	Excellent	Good	1.60	#12-860	€88,50 Qty 5+ €84,50	3-4 days
165H	1	Glass to Glass	Excellent	Excellent	1.65	#17-362	€88,50 Qty 5+ €83,90	3-4 days
170	1	Glass to Glass	Excellent	Good	1.70	#12-851	€265,00 Qty 5+ €252,10	In Stock
170F	1	Glass to Glass	Excellent	Good	1.70	#14-794	€265,00 Qty 5+ €252,10	3-4 days

1348	1	Glass to Glass	Good	Good	1.348	#12-857	€177,00 Qty 5+ €168,30	3-4 days
1369	1	Glass to Glass	Good	Good	1.369	#17-352	€203,00 Qty 5+ €197,20	3-4 days
1375	1	Glass to Glass	Excellent	Good	1.375	#17-353	€118,00 Qty 5+ €112,20	3-4 days
1422	1	Glass to Glass	Excellent	Good	1.422	#17-357	€203,00 Qty 5+ €197,20	3-4 days
13775	1	Glass to Glass	Good	Good	1.3775	#17-354	€203,00 Qty 5+ €197,20	3-4 days
13825	1	Glass to Glass	Good	Good	1.3825	#17-355	€203,00 Qty 5+ €197,20	3-4 days
1622H	1	Glass to Glass	Excellent	Excellent	1.622	#17-360	€118,00 Qty 5+ €112,20	Contact Us
1639H	1	Glass to Glass	Excellent	Excellent	1.639	#17-361	€118,00 Qty 5+ €112,20	Contact Us
1665	1	Glass to Glass	Excellent	Good	1.665	#12-863	€118,00 Qty 5+ €112,20	3-4 days
13685	1	Glass to Glass	Excellent	Good	1.3685	#12-854	€118,00 Qty 5+ €112,20	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com