

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#)

Gradient Index (GRIN) Rod Lenses




- Ideal for Fiber Coupling and Laser Diode Applications
- Comparable Performance to Conventional Aspherical Singlets
- Multiple Sizes and Wavelength Options
- [GRIN Lens Grippers and Table Mounts](#) Available

Common Specifications

Physical & Mechanical Properties					
Clear Aperture (%):		90.00	Length Tolerance (%):	±5	
Optical Properties					
Substrate:			Aluminosilicate Glass Embedded with Silver Ions	Surface Quality:	40-20
Working Distance Tolerance (mm):			±0.02		

Technical Information



Products

Dia. (mm)	Substrate	Type	Coating	EFL (mm)	NA	Stock Number	Price	Buy
0.35	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.30	0.55	#88-355	€86,52 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.54	#64-515	€60,77 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.88	0.54	#64-517	€60,77 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.67	0.52	#64-519	€60,77 Volume Pricing	5 In Stock
#64-520 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.52		€60,77 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.53	#64-521	€60,77 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.89	0.54	#64-523	€60,77 Volume Pricing	20+ In Stock

1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-524	€60,77 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.68	0.52	#64-525	€60,77 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.70	0.51	#64-526	€60,77 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.46	0.52	#64-527	€60,77 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-529	€60,77 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.51	#64-531	€60,77 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.45	0.54	#64-533	€72,10 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.88	0.54	#64-535	€72,10 Volume Pricing	Contact Us
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.67	0.52	#64-537	€72,10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.69	0.52	#64-538	€72,10 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.45	0.53	#64-539	€72,10 Volume Pricing	8 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.89	0.54	#64-541	€72,10 Volume Pricing	20+ In Stock

1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.68	0.52	#64-543	€72,10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.70	0.51	#64-544	€72,10 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.46	0.52	#64-545	€72,10 Volume Pricing	11 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.90	0.53	#64-547	€72,10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.71	0.51	#64-549	€72,10 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.72	0.51	#64-550	€72,10 Volume Pricing	20+ In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
 Phone: 1-800-363-1992 :
www.edmundoptics.com