

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® Near-UV (NUV) Achromatic Lenses



- Excellent Transmission in 345 – 700nm Range
- Ideal for use with NUV LEDs and Mercury Lamps
- Low-Cost, Cemented Design

Common Specifications



Physical & Mechanical Properties

Centering (arcmin):	<1	Bevel:	Protective bevel as needed
---------------------	----	--------	----------------------------

Optical Properties

Focal Length Tolerance (%):	±1	Focal Length Specification Wavelength (nm):	405.00
Substrate:	N-FK5 / F2HT	Surface Quality:	40-20
Coating:	UV-VIS (345-700nm)	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4	Wavelength Range (nm):	345 - 700

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Substrate	Coating	Stock Number	Price	Buy
6.25	12.50	10.22	N-FK5 / F2HT	UV-VIS (345-700nm)	#84-327	€130,00 Qty 6+ €104,00	In Stock
6.25	15.00	13.05	N-FK5 / F2HT	UV-VIS (345-700nm)	#84-328	€130,00 Qty 6+ €104,00	In Stock
#84-331 Clearance							
× Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
6.25	30.00	28.39	N-FK5 / F2HT	UV-VIS (345-700nm)		€109,00	3-4 days
9.00	18.00	15.05	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-993	€138,00 Qty 6+ €110,00	In Stock
9.00	27.00	24.13	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-994	€138,00 Qty 6+ €110,00	3-4 days
9.00	36.00	33.56	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-995	€138,00 Qty 6+ €110,00	In Stock
12.50	25.00	21.59	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-971	€142,00 Qty 6+ €114,00	In Stock

12.50	30.00	27.22	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-972	€142,00 Qty 6+ €114,00	3-4 days
12.50	40.00	37.48	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-973	€142,00 Qty 6+ €114,00	In Stock
12.50	50.00	47.31	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-974	€142,00 Qty 6+ €114,00	In Stock
25.00	50.00	44.74	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-976	€165,00 Qty 6+ €132,00	In Stock
25.00	60.00	55.63	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-977	€165,00 Qty 6+ €132,00	In Stock
25.00	75.00	71.09	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-978	€165,00 Qty 6+ €132,00	In Stock
25.00	100.00	96.32	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-979	€165,00 Qty 6+ €132,00	In Stock
25.00	125.00	121.29	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-980	€165,00 Qty 6+ €132,00	In Stock
50.00	100.00	87.39	N-FK5 / F2HT	UV-VIS (345-700nm)	#85-878	€248,00 Qty 6+ €198,00	3-4 days
50.00	150.00	141.28	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-996	€248,00 Qty 6+ €198,00	3-4 days
50.00	200.00	192.01	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-997	€248,00 Qty 6+ €198,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com