


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Color and Absorptive Filters](#)

Fluorescent Glass Filters



- Excite with UV Illumination
- Wide Range of Fluorescence Colors
- High Sensitivity and Durability

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	3.00 ±0.10
-----------------	------------

Optical Properties

Coating:	Uncoated
----------	----------


Peak Excitation Wavelength (nm):	365.00
----------------------------------	--------

Performance

Minimum Sensitivity:	~1μW/cm ²
----------------------	----------------------

Technical Information

Fluorescent Glass Filters Emission 365nm Excitation



Products

Dia. (mm)	Dimensions (mm)	Color	Stock Number	Price	Buy
12.50	-	Red	#84-883	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Red	#66-298	€287,00 Qty 10+ €254,00	3-4 days
-	50.0 x 50.0	Red	#84-886	€720,00 Qty 10+ €631,00	3-4 days
12.50	-	Orange	#21-164	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Orange	#21-168	€287,00 Qty 10+ €254,00	3-4 days
12.50	-	Yellow	#21-165	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Yellow	#21-169	€287,00 Qty 10+ €254,00	3-4 days
12.50	-	Green	#84-884	€186,00 Qty 10+ €164,00	Contact Us
25.00	-	Green	#66-300	€287,00 Qty 10+ €254,00	3-4 days
-	50.0 x 50.0	Green	#84-887	€720,00 Qty 10+ €631,00	Contact Us
12.50	-	Light Blue	#21-166	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Light Blue	#21-170	€287,00 Qty 10+ €254,00	3-4 days
12.50	-	Blue	#84-885	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Blue	#66-299	€287,00 Qty 10+ €254,00	In Stock
-	50.0 x 50.0	Blue	#84-888	€720,00 Qty 10+ €631,00	3-4 days
12.50	-	Purple	#21-167	€186,00 Qty 10+ €164,00	3-4 days
25.00	-	Purple	#21-171	€287,00 Qty 10+ €254,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com