

[All Products](#) / [Microscopy](#) / [Microscopy Cameras](#) / [USB Cameras](#)

Teledyne Lumenera INFINITY5/3/2 Microscopy Cameras

See More by [Teledyne Lumenera](#)



- Ideal for Life Sciences, Clinical, and Industrial Applications
- USB or HDMI Video Output Options
- Powerful Capture and Analysis Software Included
- PC & Mac Compatibility



Common Specifications

General

Manufacturer:	Teledyne Lumenera	Camera Family:	INFINITY
---------------	-------------------	----------------	----------

Physical & Mechanical Properties

Dimensions (mm):	97.8 x 69.8 x 50.8 (excludes lens mount)	Housing:	Full
------------------	--	----------	------

Sensor

Image Buffer:	Not Specified	Type of Shutter:	Global
---------------	---------------	------------------	--------

Hardware & Interface Connectivity

Power Supply:	Power over USB	Synchronization:	Hardware Trigger (GPIO)
Interface Port Orientation:	Side Panel	GPIO Connector Type:	8-pin Hirose (MRX)

Threading & Mounting


Mounting Threads:	2 x ¼-20 (Integrated into Housing)	Mount:	C-Mount
-------------------	------------------------------------	--------	---------

Environmental & Durability Factors

Operating Temperature (°C):	0 to +50	Storage Temperature (°C):	-30 to +70
-----------------------------	----------	---------------------------	------------

**Technical Information**

Products

Type	Model Number	Camera Sensor Format	Resolution (MegaPixels)	Mount	Housing	Stock Number	Price	Buy
<a href="#">#33-275 Clearance</a>								
Monochrome Microscopy Camera	INFINITY3-3UR	2/3"	2.80	C-Mount	Full		€4.925,00	3-4 days
						Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
Monochrome Microscopy Camera	INFINITY5-3M	1/1.8"	3.00	C-Mount	Full	<a href="#">#16-677</a>	€3.725,00	3-4 days
Color Microscopy Camera	INFINITY5-3C	1/1.8"	3.00	C-Mount	Full	<a href="#">#16-678</a>	€3.725,00	3-4 days
Monochrome Microscopy Camera	INFINITY5-5M	2/3"	5.10	C-Mount	Full	<a href="#">#16-679</a>	€4.275,00	3-4 days
Color Microscopy Camera	INFINITY5-5C	2/3"	5.10	C-Mount	Full	<a href="#">#16-680</a>	€4.275,00	Contact Us

#16-680-RCD-05P Recertified



Recertified

Stock No.: 16-680-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

Recertified  
Products

Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold  
as new for the following reasons:

- Open Box – Missing original  
packaging
- Cosmetic Blemishes –  
Scratches, rub marks or other  
minor cosmetic imperfections
- Service/Repair – Product has  
been serviced to the factory  
original specification
- Factory Returns – Product has  
been returned in its original  
condition

Recertified products are inspected for  
damage and any necessary repairs are  
made. Products are then certified by  
Edmund Optics® to be in good working  
order. Since quantity is low, recertified  
products are sold on a first come, first  
serve basis. Any imperfections will be  
listed in the description, indicated in the  
stock number, and categorized by the  
table below. When purchasing  
recertified products, the Edmund  
Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the  
Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		



C- Mount Full

3-4 days