


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Light Pipes and Homogenizing Rods](#)

TECHSPEC®

N-BK7 Light Pipe Homogenizing Rods



- Homogenizes Non-Uniform Light Sources
- Hexagonal Entrance Aperture
- Uncoated and VIS-EXT Coated Options Available
- Ideal for OEM Illumination
- Additional [Light Pipe Homogenizing Rods](#) Available

Common Specifications


Physical & Mechanical Properties

Parallelism (arcmin):	<5.00
-----------------------	-------

Optical Properties

Substrate:	N-BK7		
Surface Quality:	60-40	Aperture Tolerance (mm):	±0.10
Image Orientation:	Light Homogenization		

Technical Information



Products

Entrance and Exit Aperture (mm)	Wavelength Range (nm)	Length (mm)	Stock Number	Price	Buy
2.00	350 - 2200	25.00	#48-582	€136,99 Volume Pricing	20+ In Stock
2.00	350 - 2200	50.00	#63-080	€142,14 Volume Pricing	20+ In Stock
2.00	350 - 2200	75.00	#63-081	€170,98 Volume Pricing	17 In Stock
4.00	350 - 2200	25.00	#63-082	€107,12 Volume Pricing	4 In Stock
4.00	350 - 2200	50.00	#49-402	€120,51 Volume Pricing	20+ In Stock
4.00	350 - 2200	100.00	#63-083	€142,14 Volume Pricing	17 In Stock
5.00	350 - 2200	30.00	#63-084	€115,36 Volume Pricing	14 In Stock
5.00	350 - 2200	60.00	#48-583	€128,75 Volume Pricing	20+ In Stock
5.00	350 - 2200	120.00	#63-085	€155,53 Volume Pricing	20+ In Stock
6.00	350 - 2200	50.00	#63-086	€120,51 Volume Pricing	20+ In Stock
6.00	350 - 2200	75.00	#49-403	€136,99 Volume Pricing	20+ In Stock
6.00	350 - 2200	150.00	#63-087	€163,77 Volume Pricing	15 In Stock
8.00	350 - 2200	50.00	#63-088	€136,99 Volume Pricing	20+ In Stock
8.00	350 - 2200	100.00	#49-404	€150,38 Volume Pricing	17 In Stock
10.00	350 - 2200	75.00	#63-090	€155,53 Volume Pricing	5 In Stock
10.00	350 - 2200	125.00	#48-584	€170,98 Volume Pricing	20+ In Stock
10.00	350 - 2200	175.00	#63-091	€184,37 Volume Pricing	Contact Us

12.5	350 - 2200	75.00	#84-529	€163,77 Volume Pricing	20+ In Stock
12.5	350 - 2200	150.00	#84-530	€179,22 Volume Pricing	14 In Stock
12.5	350 - 2200	250.00	#84-531	€214,24 Volume Pricing	5 In Stock
15.0	350 - 2200	100.00	#84-532	€200,85 Volume Pricing	20+ In Stock
15.0	350 - 2200	300.00	#84-534	€272,95 Volume Pricing	6 In Stock
20.0	350 - 2200	200.00	#84-536	€272,95 Volume Pricing	20+ In Stock
20.0	350 - 2200	125.00	#84-535	€232,78 Volume Pricing	20+ In Stock
20.0	350 - 2200	300.00	#84-537	€348,14 Volume Pricing	20+ In Stock
2.00	350 - 700	25.00	#72-725	€179,22 Volume Pricing	5 In Stock
2.00	350 - 700	50.00	#72-726	€184,37 Volume Pricing	5 In Stock
2.00	350 - 700	75.00	#72-727	€214,24 Volume Pricing	Contact Us
4.00	350 - 700	25.00	#72-728	€150,38 Volume Pricing	4 In Stock
4.00	350 - 700	50.00	#72-729	€163,77 Volume Pricing	5 In Stock
4.00	350 - 700	100.00	#72-730	€184,37 Volume Pricing	2 In Stock
5.00	350 - 700	30.00	#72-731	€157,59 Volume Pricing	5 In Stock
5.00	350 - 700	60.00	#72-732	€170,98 Volume Pricing	2 In Stock
5.00	350 - 700	120.00	#72-733	€197,76 Volume Pricing	2 In Stock
6.00	350 - 700	50.00	#72-734	€163,77 Volume Pricing	4 In Stock
6.00	350 - 700	75.00	#72-735	€179,22 Volume Pricing	3 In Stock
6.00	350 - 700	150.00	#72-736	€206,00 Volume Pricing	2 In Stock

8.00	350 - 700	50.00	#72-737	€184,37 Volume Pricing	3 In Stock
8.00	350 - 700	100.00	#72-738	€197,76 Volume Pricing	1 In Stock
10.00	350 - 700	75.00	#72-739	€203,94 Volume Pricing	3 In Stock
10.00	350 - 700	125.00	#72-740	€219,39 Volume Pricing	5 In Stock
10.00	350 - 700	175.00	#72-741	€232,78 Volume Pricing	2 In Stock
12.50	350 - 700	75.00	#72-742	€211,15 Volume Pricing	2 In Stock
12.50	350 - 700	150.00	#72-743	€227,63 Volume Pricing	2 In Stock
#72-744 New					
 New					
12.50	350 - 700	250.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€262,65 Volume Pricing	5 In Stock
15.00	350 - 700	100.00	#72-745	€254,41 Volume Pricing	Contact Us
#72-746 New					
 New					
15.00	350 - 700	300.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€326,51 Volume Pricing	Contact Us

[#72-747 New](#)



New

20.00

350 - 700

200.00

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€331,66
[Volume Pricing](#)

5 In Stock

[#72-748 New](#)



New

20.00

350 - 700

125.00

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€291,49
[Volume Pricing](#)

1 In Stock

[#72-749 New](#)



New

20.00

350 - 700

300.00

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

€406,85
[Volume Pricing](#)

Contact Us



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com