

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

TECHSPEC® M25.5 and M30.5 Mounted Neutral Density Filters



- VIS and NIR ND Filters, Mounted for Imaging Lenses
- Variety of Optical Densities
- Stack Filters Together for Custom Transmission Profiles

Common Specifications

Physical & Mechanical Properties

Clear Aperture CA (mm):

22.0

Technical Information

Products

Dia. (mm)	Filter Thread	Optical Density OD (Average)	Transmission (%)	Wavelength Range (nm)	Stock Number	Price	Buy
28.00	M25.5 x 0.50	0.1	79.00	400 - 700	#66-699	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.15	70.00	400 - 700	#66-700	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.2	63.00	400 - 700	#66-701	€80,00 Qty 10+ €72,00	3-4 days
28.00	M25.5 x 0.50	0.3	50.00	400 - 700	#66-702	€80,00 Qty 10+ €72,00	3-4 days
28.00	M25.5 x 0.50	0.4	40.00	400 - 700	#66-703	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.5	32.00	400 - 700	#66-704	€80,00 Qty 10+ €72,00	3-4 days
28.00	M25.5 x 0.50	0.6	25.00	400 - 700	#66-705	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.7	20.00	400 - 700	#66-706	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.9	12.50	400 - 700	#66-707	€80,00 Qty 10+ €72,00	3-4 days
28.00	M25.5 x 0.50	1.0	10.00	400 - 700	#66-708	€80,00 Qty 10+ €72,00	3-4 days
28.00	M25.5 x 0.50	1.3	5.00	400 - 700	#66-709	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	1.5	3.20	400 - 700	#66-710	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	2.0	1.00	400 - 700	#66-711	€80,00 Qty 10+ €72,00	In Stock
28.00	M25.5 x 0.50	2.5	0.30	400 - 700	#66-712	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	3.0	0.10	400 - 700	#66-713	€80,00 Qty 10+ €72,00	3-4 days
33.50	M30.5 x 0.50	0.1	79.00	400 - 700	#66-714	€80,00 Qty 10+ €72,00	Contact Us

33.50	M30.5 x 0.50	0.15	70.00	400 - 700	#66-715	€80,00 Qty 10+ €72,00	3-4 days
33.50	M30.5 x 0.50	0.2	63.00	400 - 700	#66-716	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	0.3	50.00	400 - 700	#66-717	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	0.4	40.00	400 - 700	#66-718	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	0.5	32.00	400 - 700	#66-719	€80,00 Qty 10+ €72,00	3-4 days
33.50	M30.5 x 0.50	0.6	25.00	400 - 700	#66-720	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	0.7	20.00	400 - 700	#66-721	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	0.9	12.50	400 - 700	#66-722	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	1.0	10.00	400 - 700	#66-723	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	1.3	5.00	400 - 700	#66-724	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	1.5	3.20	400 - 700	#66-725	€80,00 Qty 10+ €72,00	Contact Us
33.50	M30.5 x 0.50	2.0	1.00	400 - 700	#66-726	€80,00 Qty 10+ €72,00	3-4 days
33.50	M30.5 x 0.50	2.5	0.30	400 - 700	#66-727	€80,00 Qty 10+ €72,00	3-4 days
33.50	M30.5 x 0.50	3.0	0.10	400 - 700	#66-728	€80,00 Qty 10+ €72,00	Contact Us
28.00	M25.5 x 0.50	0.3	50.00	700 - 1200	#66-729	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	0.5	32.00	700 - 1200	#66-730	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	0.6	25.00	700 - 1200	#66-731	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	0.9	12.50	700 - 1200	#66-732	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	1.0	10.00	700 - 1200	#66-733	€145,00 Qty 10+ €130,00	Contact Us

28.00	M25.5 x 0.50	1.3	5.00	700 - 1200	#66-734	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	1.5	3.20	700 - 1200	#66-735	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	2.0	1.00	700 - 1200	#66-736	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	2.5	0.30	700 - 1200	#66-737	€145,00 Qty 10+ €130,00	Contact Us
28.00	M25.5 x 0.50	3.0	0.10	700 - 1200	#66-738	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	0.3	50.00	700 - 1200	#66-739	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	0.5	32.00	700 - 1200	#66-740	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	0.6	25.00	700 - 1200	#66-741	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	0.9	12.50	700 - 1200	#66-742	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	1.0	10.00	700 - 1200	#66-743	€145,00 Qty 10+ €130,00	3-4 days
33.50	M30.5 x 0.50	1.3	5.00	700 - 1200	#66-744	€145,00 Qty 10+ €130,00	3-4 days
33.50	M30.5 x 0.50	1.5	3.20	700 - 1200	#66-745	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	2.0	1.00	700 - 1200	#66-746	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	2.5	0.30	700 - 1200	#66-747	€145,00 Qty 10+ €130,00	Contact Us
33.50	M30.5 x 0.50	3.0	0.10	700 - 1200	#66-748	€145,00 Qty 10+ €130,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com