

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

IDS Imaging uEye CP/SE GigE PoE Cameras See More by [IDS Imaging Development Systems](#)



- Standard (SE) and Compact (CP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- GenICam GigE Vision Compliant
- [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#) Available

Common Specifications

Manufacturer:		IDS Imaging Development Systems	
Housing:	Full		
Image Buffer:	128MB	Type of Sensor:	Progressive Scan CMOS
Machine Vision Standard:	GigE Vision		
Interface:	GigE (PoE)		
GPIOs:	2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	Synchronization:	Hardware Trigger (GPIO); Software Trigger
Interface Port Orientation:	Back Panel		
Mount:	C-Mount		
Operating Temperature (°C):	0 to +55	Storage Temperature (°C):	-20 to +60

Technical Information

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price
Color Camera	GV-5240CP-C-HQ	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-229	€595,00
Monochrome Camera	GV-5240CP-M-GL	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-230	€595,00
Mono NIR	GV-5240CP-NIR-GL	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-232	€745,00
Color Camera	GV-5240SE-C-HQ	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-260	€765,00
Monochrome Camera	GV-5240SE-M-GL	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-261	€765,00
Mono NIR	GV-5240SE-NIR-GL	1/1.8"	1.31	GigE RJ45, screwable	C-Mount	#26-262	€885,00
Color Camera	GV-5250CP-C-HQ	1/1.8"	1.90	GigE RJ45, screwable	C-Mount	#26-233	€685,00
Monochrome Camera	GV-5250CP-M-GL	1/1.8"	1.90	GigE RJ45, screwable	C-Mount	#26-234	€685,00
Color Camera	GV-5250SE-C-HQ	1/1.8"	1.92	GigE RJ45, screwable	C-Mount	#26-263	€855,00
Monochrome Camera	GV-5250SE-M-GL	1/1.8"	1.92	GigE RJ45, screwable	C-Mount	#26-264	€855,00
Color Camera	GV-5880CP-C-HQ	1/1.8"	6.41	GigE RJ45, screwable	C-Mount	#26-247	€530,00
Monochrome Camera	GV-5880CP-M-GL	1/1.8"	6.41	GigE RJ45, screwable	C-Mount	#26-248	€530,00
Color Camera	GV-5880SE-C-HQ	1/1.8"	6.41	GigE RJ45, screwable	C-Mount	#26-280	€700,00
Monochrome Camera	GV-5880SE-M-GL	1/1.8"	6.41	GigE RJ45, screwable	C-Mount	#26-281	€700,00
Color Camera	GV-5800SE-C-HQ	1"	20.44	GigE RJ45, screwable	C-Mount	#26-276	€1.000,00
Monochrome Camera	GV-5800SE-M-GL	1"	20.44	GigE RJ45, screwable	C-Mount	#26-277	€1.000,00

Color Camera	GV-5890CP-C-HQ	1/1.7"	12.00	GigE RJ45, screwable	C-Mount	#26-250	€595,00
Monochrome Camera	GV-5890CP-M-GL	1/1.7"	12.00	GigE RJ45, screwable	C-Mount	#26-252	€595,00
Color Camera	GV-5890SE-C-HQ	1/1.7"	12.00	GigE RJ45, screwable	C-Mount	#26-282	€765,00
Monochrome Camera	GV-5890SE-M-GL	1/1.7"	12.00	GigE RJ45, screwable	C-Mount	#26-283	€765,00
Color Camera	GV-5260CP-C-HQ	1/1.2"	2.30	GigE RJ45, screwable	C-Mount	#26-236	€695,00
Monochrome Camera	GV-5260CP-M-GL	1/1.2"	2.30	GigE RJ45, screwable	C-Mount	#26-237	€695,00
Color Camera	GV-5260SE-C-HQ	1/1.2"	2.30	GigE RJ45, screwable	C-Mount	#26-265	€865,00
Monochrome Camera	GV-5260SE-M-GL	1/1.2"	2.30	GigE RJ45, screwable	C-Mount	#26-266	€865,00
Mono POL	GV-5080CP-P-GL	2/3"	5.01	GigE RJ45, screwable	C-Mount	#26-226	€2.985,00
Color Camera	GV-5280CP-C-HQ	2/3"	5.01	GigE RJ45, screwable	C-Mount	#26-240	€1.010,00
Monochrome Camera	GV-5280CP-M-GL	2/3"	5.01	GigE RJ45, screwable	C-Mount	#26-241	€1.010,00
Color Camera	GV-5280SE-C-HQ	2/3"	5.01	GigE RJ45, screwable	C-Mount	#26-269	€1.180,00
Monochrome Camera	GV-5280SE-M-GL	2/3"	5.01	GigE RJ45, screwable	C-Mount	#26-270	€1.180,00
Color Camera	GV-5270CP-C-HQ	1/1.8"	3.19	GigE RJ45, screwable	C-Mount	#26-238	€670,00
Monochrome Camera	GV-5270CP-M-GL	1/1.8"	3.19	GigE RJ45, screwable	C-Mount	#26-239	€670,00
Color Camera	GV-5270SE-C-HQ	1/1.8"	3.19	GigE RJ45, screwable	C-Mount	#26-267	€840,00
Monochrome Camera	GV-5270SE-M-GL	1/1.8"	3.19	GigE RJ45, screwable	C-Mount	#26-268	€840,00
Color Camera	GV-5290SE-C-HQ	1"	8.85	GigE RJ45, screwable	C-Mount	#26-271	€1.945,00

Monochrome Camera	GV-5290SE-M-GL	1"	8.85	GigE RJ45, screwable	C-Mount	#26-272	€1.945,00
Color Camera	GV-5040CP-C-HQ	1/2.9"	1.58	GigE RJ45, screwable	C-Mount	#26-224	€540,00
Monochrome Camera	GV-5040CP-M-GL	1/2.9"	1.58	GigE RJ45, screwable	C-Mount	#26-225	€540,00

Monochrome Camera GV-5040CP-M-GL 1/2.9" 1.58 GigE RJ45, screwable C-Mount

[#26-225-RCD-05P Recertified](#)

€410,00



Recertified

Stock No.: 26-225-RCD-05P
 Recertified Code: 05P (All Original Parts Included, Perfect)

Recertified Products

Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.

Recertified products are those identified with the recertified logo indicating they were returned to Edmund Optics® and cannot be sold as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual		

and Large
Accessory

Color Camera	GV-5040SE-C-HQ	1/2.9"	1.58	GigE RJ45, screwable	C-Mount	#26-253	€710,00
Monochrome Camera	GV-5040SE-M-GL	1/2.9"	1.58	GigE RJ45, screwable	C-Mount	#26-254	€710,00
Monochrome Camera	GV-51F0CP-M-GL	1/1.8"	5.10	GigE RJ45, screwable	C-Mount	#78-097	€765,00
Color Camera	GV-51J0CP-C-HQ	2/3"	8.13	GigE RJ45, screwable	C-Mount	#78-094	€960,00
Monochrome Camera	GV-51J0CP-M-GL	2/3"	8.13	GigE RJ45, screwable	C-Mount	#78-095	€960,00
Color Camera	GV-51L0CP-C-HQ	1/1.1"	12.42	GigE RJ45, screwable	C-Mount	#78-092	€1.555,00
Monochrome Camera	GV-51L0CP-M-GL	1/1.1"	12.42	GigE RJ45, screwable	C-Mount	#78-093	€1.555,00
Color Camera	GV-51N0CP-C-HQ	1.1"	16.20	GigE RJ45, screwable	C-Mount	#78-102	€1.840,00
Monochrome Camera	GV-51N0CP-M-GL	1.1"	16.20	GigE RJ45, screwable	C-Mount	#78-103	€1.840,00
Color Camera	GV-51R0CP-C-HQ	1.2"	24.55	GigE RJ45, screwable	C-Mount	#78-100	€2.830,00
Monochrome Camera	GV-51R0CP-M-GL	1.2"	24.55	GigE RJ45, screwable	C-Mount	#78-101	€2.830,00
Color Camera	GV-5860CP-C-HQ	1/3"	2.12	GigE RJ45, screwable	C-Mount	#26-245	€585,00
Monochrome Camera	GV-5860CP-M-GL	1/3"	2.12	GigE RJ45, screwable	C-Mount	#26-246	€585,00
Color Camera	GV-5860SE-C-HQ	1/3"	2.12	GigE RJ45, screwable	C-Mount	#26-278	€750,00
Monochrome Camera	GV-5860SE-M-GL	1/3"	2.12	GigE RJ45, screwable	C-Mount	#26-279	€750,00
Color Camera	GV-5200SE-C-HQ	1.1"	12.29	GigE RJ45, screwable	C-Mount	#26-258	€2.415,00

Monochrome Camera	GV-5200SE-M-GL	1.1"	12.29	GigE RJ45, screwable	C-Mount	#26-259	€2.415,00
Color Camera	GV-50C0CP-C-HQ	1/2.3"	2.35	GigE RJ45, screwable	C-Mount	#26-227	€545,00
Monochrome Camera	GV-50C0CP-M-GL	1/2.3"	2.35	GigE RJ45, screwable	C-Mount	#26-228	€545,00
Color Camera	GV-50C0SE-C-HQ	1/2.3"	2.35	GigE RJ45, screwable	C-Mount	#26-255	€715,00
Monochrome Camera	GV-50C0SE-M-GL	1/2.3"	2.35	GigE RJ45, screwable	C-Mount	#26-256	€715,00
Color Camera	GV-5990SE-C-HQ	1.1"	20.36	GigE RJ45, screwable	C-Mount	#26-284	€2.505,00
Monochrome Camera	GV-5990SE-M-GL	1.1"	20.36	GigE RJ45, screwable	C-Mount	#26-285	€2.505,00
#26-275 Clearance							
Color Camera	GV-5580SE-C-HQ Rev.4.2	1/2.5"	4.92	GigE, RJ45 with Screw Locks	C-Mount	<p style="text-align: center;">Clearance</p> <p>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</p>	€755,00
Monochrome Camera	GV-5990CP-M-GL	1.1"	20.36	GigE RJ45, screwable	C-Mount	#78-099	€2.335,00
Color Camera	GV-5990CP-C-HQ	1.1"	20.36	GigE RJ45, screwable	C-Mount	#78-098	€2.335,00
Color Camera	GV-51F0CP-C-HQ	1/1.8"	5.10	GigE RJ45, screwable	C-Mount	#78-096	€790,00



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands
 Phone: 1-800-363-1992 :
www.edmundoptics.com