

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

# Advanced Illumination UltraSeal Washdown Backlights See

 More by [Advanced Illumination](#)


- IP69K Certified for Extreme Washdown Environments
- Proprietary Housing to Prevent Corrosion and Overheating
- Intensity Output up to 15,000 Lux
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

## Common Specifications

### General

<b>LED Lifetime (hours):</b>	50000	<b>Type of Illumination:</b>	LED Illuminator
<b>Note:</b>	Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available	<b>Manufacturer:</b>	Advanced Illumination
<b>Geometry:</b>	Backlight	<b>Illumination Mode:</b>	Constant

### Hardware & Interface Connectivity


<b>Input Voltage (V):</b>	24V	<b>Power Supply:</b>	Power Supply Required and Sold Separately: USA: <a href="#">#66-855</a> Europe: <a href="#">#66-855</a> Japan: <a href="#">#66-855</a> Korea: <a href="#">#33-773</a> China: <a href="#">#66-855</a>
---------------------------	-----	----------------------	---

### Environmental & Durability Factors

<b>Operating Temperature (°C):</b>	0 - 60	<b>Environmental Rating:</b>	IP69K
------------------------------------	--------	------------------------------	-------

## Technical Information

## Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
122.2 x 122.2 x 24.0	White	-	<a href="#">#18-608</a>	€1.185,00	Contact Us
122.2 x 122.2 x 24.0	Blue	470.00	<a href="#">#18-610</a>	€1.185,00	3-4 days
122.2 x 122.2 x 24.0	Green	520.00	<a href="#">#18-611</a>	€1.185,00	3-4 days
<a href="#">#18-609 Clearance</a>					
 <p>Clearance</p> <p>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</p>					
122.2 x 122.2 x 24.0	Red	660.00		€1.075,00	3-4 days
122.2 x 122.2 x 24.0	IR	880.00	<a href="#">#18-612</a>	€1.175,00	3-4 days
173.0 x 173.0 x 24.0	White	-	<a href="#">#18-618</a>	€1.660,00	3-4 days
173.0 x 173.0 x 24.0	Blue	470.00	<a href="#">#18-620</a>	€1.660,00	3-4 days
173.0 x 173.0 x 24.0	Green	520.00	<a href="#">#18-621</a>	€1.582,00	3-4 days

[#18-619 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

173.0 x 173.0 x 24.0	Red	660.00	€1.345,00	3-4 days
-------------------------	-----	--------	-----------	----------

173.0 x 173.0 x 24.0	IR	880.00	<a href="#">#18-622</a>	€1.635,00	3-4 days
-------------------------	----	--------	-------------------------	-----------	----------

223.8 x 122.2 x 24.0	White	-	<a href="#">#18-613</a>	€1.560,00	3-4 days
-------------------------	-------	---	-------------------------	-----------	----------

223.8 x 122.2 x 24.0	Blue	470.00	<a href="#">#18-615</a>	€1.485,00	3-4 days
-------------------------	------	--------	-------------------------	-----------	----------

223.8 x 122.2 x 24.0	Green	520.00	<a href="#">#18-616</a>	€1.560,00	3-4 days
-------------------------	-------	--------	-------------------------	-----------	----------

223.8 x 122.2 x 24.0	IR	880.00	<a href="#">#18-617</a>	€1.540,00	3-4 days
-------------------------	----	--------	-------------------------	-----------	----------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)