

[All Products](#) / [Clearance Products](#) / [Clearance Optics](#)

Bandpass Interference Filters





- Many CWL Options Available
- Ideal for Biomedical Applications and Instrumentation Integration
- Unmounted and Mounted Versions Offered

Common Specifications

Optical Properties			
Optical Density OD (Average):	≥3.0	Coating:	Traditional Coated
Surface Quality:	80-50	Blocking Wavelength Range (nm):	200 - 1200
Angle Sensitivity:	Intended for Collimated Input		
Environmental & Durability Factors			
Operating Temperature (°C):	-50 to +75		

Technical Information

Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Minimum Transmission (%)	Blocking Wavelength Range (nm)	Dimensions (mm)	Stock Number	Price	Buy
#43-092 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
11.80	766.00	10.00	≥50	200 - 1200	-		€14,95	3-4 days
#46-154 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
11.80	700.00	80.00	60.00	200 - 1200	-		€18,95	3-4 days

[#62-119 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.70	766.00	10.00	≥50	200 - 1200	-	€16,95	3-4 days
-------	--------	-------	-----	------------	---	--------	----------

[#43-056 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

11.80	430.00	10.00	≥40	200 - 1200	-	€14,95	3-4 days
-------	--------	-------	-----	------------	---	--------	----------

[#43-057 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

11.80	436.00	10.00	≥40	200 - 1200	-	€14,95	3-4 days
-------	--------	-------	-----	------------	---	--------	----------

[#62-080 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.70	436.00	10.00	≥40	200 - 1200	-	€16,95	Contact Us
-------	--------	-------	-----	------------	---	--------	------------

[#62-797 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.70	450.00	80.00	60.00	200 - 1200	-	€20,00	3-4 days
-------	--------	-------	-------	------------	---	--------	----------

