

[All Products](#) / [Optomechanics](#) / [Optical Cage System](#) / [Cage System Optical Mounts](#)

TECHSPEC®

M23.2 and M27.5 Fixed Tubes and Retaining Rings



- Fit within Inner Diameter of [Cage System Plates](#)
- Use with Retaining Ring Pairs to Secure Optics
- Join Multiple with Adjustable Length Tubes and Thread Adapters

Common Specifications

General

Function:

Fixed

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum

**Technical Information**

## Products

| Note           | Compatible Plate Inner Diameter (mm) | Length (mm) | Size of Compatible Optics (mm) | Thread Type  | Outer Diameter (mm) | Stock Number            | Price  | Buy        |
|----------------|--------------------------------------|-------------|--------------------------------|--------------|---------------------|-------------------------|--------|------------|
| Fixed Tube     | 25.0                                 | 5.00        | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-517</a> | €29,00 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 10.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-518</a> | €29,00 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 15.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-519</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 20.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-520</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 25.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-521</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 30.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-522</a> | €41,50 | 3-4 days   |
| Fixed Tube     | 25.0                                 | 50.00       | -                              | M23.2 x 0.75 | 25.0                | <a href="#">#85-523</a> | €46,75 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 5.00        | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-586</a> | €29,00 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 10.00       | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-589</a> | €29,00 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 15.00       | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-590</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 20.00       | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-593</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 25.00       | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-594</a> | €34,25 | 3-4 days   |
| Fixed Tube     | 30.0                                 | 50.00       | -                              | M27.5 x 0.75 | 30.0                | <a href="#">#85-600</a> | €46,75 | 3-4 days   |
| Retaining Ring | -                                    | 3.00        | 6.0                            | M23.2 x 0.75 | -                   | <a href="#">#85-566</a> | €34,25 | Contact Us |
| Retaining Ring | -                                    | 3.00        | 6.5                            | M23.2 x 0.75 | -                   | <a href="#">#85-565</a> | €34,25 | 3-4 days   |
| Retaining Ring | -                                    | 3.00        | 9.0                            | M23.2 x 0.75 | -                   | <a href="#">#85-564</a> | €34,25 | In Stock   |
| Retaining Ring | -                                    | 3.00        | 10.0                           | M23.2 x 0.75 | -                   | <a href="#">#85-563</a> | €34,25 | 3-4 days   |

|                |   |      |      |              |   |                         |        |          |
|----------------|---|------|------|--------------|---|-------------------------|--------|----------|
| Retaining Ring | - | 3.00 | 12.0 | M23.2 x 0.75 | - | <a href="#">#85-562</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 12.5 | M23.2 x 0.75 | - | <a href="#">#85-561</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 12.7 | M23.2 x 0.75 | - | <a href="#">#85-560</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 15.0 | M23.2 x 0.75 | - | <a href="#">#85-559</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 18.0 | M23.2 x 0.75 | - | <a href="#">#85-558</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 20.0 | M23.2 x 0.75 | - | <a href="#">#85-556</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 25.0 | M27.5 x 0.75 | - | <a href="#">#85-597</a> | €34,25 | 3-4 days |
| Retaining Ring | - | 3.00 | 25.4 | M27.5 x 0.75 | - | <a href="#">#85-596</a> | €34,25 | 3-4 days |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)