

[All Products](#) / [Laser Optics](#) / [Laser Beam Expanders](#) / [Vega® Beam Expanders](#)

TECHSPEC®

Vega® Laser Line Beam Expanders



- AR Coated for Laser Wavelengths: 266nm, 355nm, 405nm, 532nm, 1064nm, and 1940nm
- Fixed Magnifications Available from 1.5X to 20X
- Divergence Adjustable through Rotating Optical Design

Common Specifications

Optical Properties

Angle of Incidence (°):	0	Divergence Adjustment:	Rotating Optics
-------------------------	---	------------------------	-----------------

Technical Information

Products

DWL (nm)	Expansion Power	Wavelength Range (nm)	Entrance Aperture (mm)	Exit Aperture (mm)	Substrate	Stock Number	Price	Buy
266	2X	250 - 280	10	23	Fused Silica	#35-092	€380,00 Qty 10+ €335,00	3-4 days
266	3X	250 - 280	10	23	Fused Silica	#35-096	€380,00 Qty 10+ €335,00	3-4 days
266	4X	250 - 280	7.5	26	Fused Silica	#19-401	€395,00	3-4 days
266	5X	250 - 280	7.5	26	Fused Silica	#35-100	€490,00 Qty 10+ €430,00	3-4 days
266	7X	250 - 280	7.5	26	Fused Silica	#35-108	€490,00 Qty 10+ €430,00	3-4 days
266	10X	250 - 280	7.5	32	Fused Silica	#35-114	€505,00 Qty 10+ €445,00	3-4 days
355	1.5X	340 - 380	10	23	Fused Silica	#12-873	€360,00 Qty 10+ €315,00	3-4 days
355	2X	340 - 380	10	23	Fused Silica	#35-093	€380,00 Qty 10+ €335,00	3-4 days
355	3X	340 - 380	10	23	Fused Silica	#35-097	€380,00 Qty 10+ €335,00	3-4 days
355	4X	340 - 380	7.5	26	Fused Silica	#19-402	€395,00	3-4 days
355	5X	340 - 380	7.5	26	Fused Silica	#35-101	€490,00 Qty 10+ €430,00	Contact Us
355	7X	340 - 380	7.5	26	Fused Silica	#35-109	€490,00 Qty 10+ €430,00	3-4 days
355	10X	340 - 380	7.5	26	Fused Silica	#35-115	€505,00 Qty 10+ €445,00	3-4 days
355	20X	340 - 380	4.5	32	Fused Silica	#35-119	€810,00 Qty 10+ €715,00	3-4 days
405	10X	375 - 435	7.5	26	Fused Silica	#37-999	€490,00 Qty 10+ €430,00	3-4 days
532	1.5X	500 - 570	10	23	Fused Silica	#12-874	€350,00 Qty 10+ €310,00	3-4 days
532	2X	500 - 570	10	23	Fused Silica	#35-094	€365,00 Qty 10+ €325,00	3-4 days
532	3X	500 - 570	10	23	Fused Silica	#35-098	€365,00 Qty 10+ €325,00	3-4 days
532	4X	500 - 570	7.5	26	Fused Silica	#19-403	€395,00	3-4 days

532	5X	500 - 570	7.5	26	Fused Silica	#35-102	€480,00 Qty 10+ €420,00	3-4 days
532	7X	500 - 570	7.5	26	Fused Silica	#35-112	€480,00 Qty 10+ €420,00	3-4 days
532	10X	500 - 570	7.5	26	Fused Silica	#35-116	€495,00 Qty 10+ €435,00	Contact Us
532	20X	500 - 570	4.5	32	Fused Silica	#35-120	€800,00 Qty 10+ €705,00	3-4 days
1064	1.5X	1000 - 1140	8	23	Fused Silica	#12-875	€350,00 Qty 10+ €310,00	3-4 days
1064	2X	1000 - 1140	8	23	Fused Silica	#35-095	€365,00 Qty 10+ €325,00	Contact Us
1064	3X	1000 - 1140	8	23	Fused Silica	#35-099	€365,00 Qty 10+ €325,00	In Stock
1064	4X	1000 - 1140	7.1	26	Fused Silica	#19-404	€395,00	3-4 days
1064	5X	1000 - 1140	7.1	26	Fused Silica	#35-103	€480,00 Qty 10+ €420,00	3-4 days
1064	7X	1000 - 1140	7.1	26	Fused Silica	#35-113	€480,00 Qty 10+ €420,00	3-4 days
1064	10X	1000 - 1140	5.45	26	Fused Silica	#35-117	€495,00 Qty 10+ €435,00	3-4 days
1064	20X	1000 - 1140	4.5	32	Fused Silica	#35-121	€800,00 Qty 10+ €705,00	3-4 days
Broadband	2X	1900 - 2100	10	23	Fused Silica	#37-357	€760,00	3-4 days
Broadband	3X	1900 - 2100	10	23	Fused Silica	#37-341	€760,00	3-4 days
Broadband	2X	1900 - 2100	10	23	Fused Silica	#37-376	€635,00	3-4 days
Broadband	3X	1900 - 2100	10	23	Fused Silica	#37-377	€635,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com