

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Pinholes and Slits](#)

Acktar Blackened Air Slits See More by [Acktar](#)



- Wide-Band Low Reflectance Coating
- 99% Absorbance from the EUV to SWIR
- Slit Sizes Down to 25µm x 3mm
- Unmounted and Mounted Versions Available

Common Specifications

Physical & Mechanical Properties

Construction: Stainless Steel

Slit Length (mm): 3.0

Optical Properties

Coating: Magic Black™

Material Properties

Absorbance (%): 99

Technical Information

Products

Type	Outer Diameter (mm)	Construction	Slit Length (mm)	Slit Width (µm)	Stock Number	Price	Buy
Unmounted	9.53	Stainless Steel	3.0	25	#12-176	€184,00 Qty 10+ €166,10	In Stock
Unmounted	9.53	Stainless Steel	3.0	50	#12-177	€184,00 Qty 10+ €166,10	3-4 days
Unmounted	9.53	Stainless Steel	3.0	75	#17-462	€184,00 Qty 10+ €166,10	3-4 days
Unmounted	9.53	Stainless Steel	3.0	100	#12-178	€184,00 Qty 10+ €166,10	Contact Us
Unmounted	9.53	Stainless Steel	3.0	150	#17-463	€184,00 Qty 10+ €166,10	3-4 days
Unmounted	9.53	Stainless Steel	3.0	200	#12-179	€184,00 Qty 10+ €166,10	3-4 days
Unmounted	9.53	Stainless Steel	3.0	500	#17-464	€184,00 Qty 10+ €166,10	In Stock
Unmounted	9.53	Stainless Steel	3.0	1000	#17-465	€184,00 Qty 10+ €166,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	25	#12-180	€194,00 Qty 10+ €175,10	In Stock
Mounted	25.0	Stainless Steel	3.0	50	#12-181	€194,00 Qty 10+ €175,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	75	#17-466	€194,00 Qty 10+ €175,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	100	#12-182	€194,00 Qty 10+ €175,10	Contact Us
Mounted	25.0	Stainless Steel	3.0	150	#17-467	€194,00 Qty 10+ €175,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	200	#12-183	€194,00 Qty 10+ €175,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	500	#17-468	€194,00 Qty 10+ €175,10	3-4 days
Mounted	25.0	Stainless Steel	3.0	1000	#17-469	€194,00 Qty 10+ €175,10	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com