

[All Products](#) / [Optomechanics](#) / [Tube System](#) / [C, S, and T-Mount Components](#)

TECHSPEC®

C, S, and T-Mount Circular Optic Mounts





- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

Common Specifications


General

|                 |          |           |                     |
|-----------------|----------|-----------|---------------------|
| Type of Optics: | Circular | Function: | Optic Mount (Fixed) |
|-----------------|----------|-----------|---------------------|


## Technical Information




### C-Mount Achromat/Thick Lens Mounts




### C-Thread Simple / Thin Lens Mount




### C-Thread Achromat / Thick Lens Mount




## S-Thread Simple / Thin Lens Mount




## C-Thread Achromat / Thick Lens Mount





## S-Thread Simple /Thin Lens Mount



## S-Thread Achromat / Thick Lens Mount





#58-741

Products

| Thread Type | Diameter of Compatible Optics (mm) | Max. Thickness of Compatible Optics (mm) | Min. Thickness of Compatible Optics (mm) | Extension Length (mm) | Stock Number            | Price                   | Buy        |
|-------------|------------------------------------|------------------------------------------|------------------------------------------|-----------------------|-------------------------|-------------------------|------------|
| C-Mount     | 25.0 - 25.4                        | 3.75                                     | 1.0                                      | 16.3                  | <a href="#">#56-353</a> | €98,00<br>Qty 5+ €87,00 | In Stock   |
| C-Mount     | 21.0                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#53-860</a> | €54,00<br>Qty 5+ €47,70 | 3-4 days   |
| C-Mount     | 20.0                               | 2.90                                     | 1.00                                     | 5.6                   | <a href="#">#54-618</a> | €54,00<br>Qty 5+ €48,00 | In Stock   |
| C-Mount     | 18.0                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-617</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount     | 15.0                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-616</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount     | 12.5                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#55-246</a> | €54,00<br>Qty 5+ €48,00 | Contact Us |
| C-Mount     | 12.0                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-615</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount     | 10.0                               | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#63-979</a> | €54,00<br>Qty 5+ €48,00 | Contact Us |
| C-Mount     | 9.0                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-614</a> | €54,00<br>Qty 5+ €48,00 | In Stock   |
| C-Mount     | 6.5                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#57-973</a> | €54,00<br>Qty 5+ €51,60 | 3-4 days   |
| C-Mount     | 6.0                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-613</a> | €54,00<br>Qty 5+ €48,00 | In Stock   |
| C-Mount     | 5.0                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-612</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount     | 4.0                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#57-972</a> | €54,00<br>Qty 5+ €50,70 | 3-4 days   |
| C-Mount     | 3.0                                | 3.0                                      | 1.0                                      | 5.6                   | <a href="#">#54-611</a> | €54,00<br>Qty 5+ €48,00 | In Stock   |
| C-Mount     | 3.0                                | 11.0                                     | 1.5                                      | 14.0                  | <a href="#">#54-620</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount     | 5.0                                | 6.5                                      | 1.0                                      | 14.0                  | <a href="#">#57-974</a> | €54,00<br>Qty 5+ €51,60 | 3-4 days   |

|         |             |      |     |      |                         |                         |            |
|---------|-------------|------|-----|------|-------------------------|-------------------------|------------|
| C-Mount | 6.25        | 11.0 | 2.5 | 14.0 | <a href="#">#54-621</a> | €54,00<br>Qty 5+ €48,00 | In Stock   |
| C-Mount | 9.0         | 11.0 | 2.5 | 14.0 | <a href="#">#54-622</a> | €54,00<br>Qty 5+ €48,00 | Contact Us |
| C-Mount | 10.0        | 10.5 | 2.0 | 14.0 | <a href="#">#63-980</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount | 12.5        | 11.0 | 2.5 | 14.0 | <a href="#">#54-623</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount | 15.0        | 11.0 | 3.0 | 14.0 | <a href="#">#54-624</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount | 18.0        | 11.0 | 3.0 | 14.0 | <a href="#">#54-625</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount | 20.0        | 11.0 | 3.5 | 14.0 | <a href="#">#54-626</a> | €54,00<br>Qty 5+ €48,00 | 3-4 days   |
| C-Mount | 25.0 - 25.4 | 11.5 | 3.3 | 24.2 | <a href="#">#56-354</a> | €98,00<br>Qty 5+ €87,00 | In Stock   |
| S-Mount | 3.0         | 3.0  | 1.0 | 6.2  | <a href="#">#63-938</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 4.0         | 3.0  | 1.0 | 6.2  | <a href="#">#63-939</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 5.0         | 3.0  | 1.0 | 5.6  | <a href="#">#63-940</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 6.0         | 3.0  | 1.0 | 5.6  | <a href="#">#63-941</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 9.0         | 3.0  | 1.0 | 5.6  | <a href="#">#63-942</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 10.0        | 2.5  | 1.0 | 8.6  | <a href="#">#63-943</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 12.5 - 12.7 | 2.5  | 1.0 | 13.6 | <a href="#">#63-944</a> | €61,00<br>Qty 5+ €54,20 | In Stock   |
| S-Mount | 5.0         | 6.5  | 1.0 | 9.7  | <a href="#">#63-948</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 6.25        | 6.5  | 2.0 | 9.7  | <a href="#">#63-949</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 9.0         | 6.5  | 2.0 | 9.7  | <a href="#">#63-950</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 10.0        | 6.5  | 2.0 | 12.7 | <a href="#">#63-951</a> | €37,00<br>Qty 5+ €33,20 | 3-4 days   |
| S-Mount | 12.5 - 12.7 | 6.5  | 2.0 | 20.5 | <a href="#">#63-952</a> | €61,00<br>Qty 5+ €54,20 | 3-4 days   |

|         |             |       |      |      |                         |                         |          |
|---------|-------------|-------|------|------|-------------------------|-------------------------|----------|
| T-Mount | 12.5 - 12.7 | 5.50  | 2.00 | 11.5 | <a href="#">#52-933</a> | €65,50<br>Qty 5+ €61,60 | 3-4 days |
| T-Mount | 25.0 - 25.4 | 5.50  | 2.00 | 11.5 | <a href="#">#52-292</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 27.0        | 5.5   | 2.0  | 11.5 | <a href="#">#53-861</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 30.0        | 5.5   | 2.5  | 11.5 | <a href="#">#57-975</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 40.0        | 10.95 | 2.0  | 15.0 | <a href="#">#57-976</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 12.5 - 12.7 | 15.50 | 5.00 | 21.5 | <a href="#">#52-954</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 25.0 - 25.4 | 15.50 | 5.00 | 21.5 | <a href="#">#52-293</a> | €65,50<br>Qty 5+ €58,30 | In Stock |
| T-Mount | 30.0        | 15.5  | 5.0  | 21.5 | <a href="#">#57-977</a> | €65,50<br>Qty 5+ €58,30 | In Stock |
| T-Mount | 40.0        | 20.95 | 5.0  | 25.0 | <a href="#">#57-978</a> | €65,50<br>Qty 5+ €58,30 | 3-4 days |
| T-Mount | 50.0        | 10.0  | 2.0  | 22.0 | <a href="#">#88-943</a> | €98,00<br>Qty 5+ €85,20 | In Stock |
| T-Mount | 50.0        | 18.5  | 5.0  | 32.5 | <a href="#">#88-944</a> | €98,00<br>Qty 5+ €85,20 | 3-4 days |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)