

[All Products](#) / [Optomechanics](#) / [TECHSPEC® Multi-Element Spacer Rings and Tubes](#)

[See all 14 Products in Family](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

TECHSPEC® 0.15mm



1

€15^{,75}

ADD TO CART

TECHSPEC Multi-Element Spacer Ring



Volume Pricing

Qty 1-4 €15,75 each

Qty 5-9 €15,20 each

Qty 10+ €14,90 each

Need More? [Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Function: Spacer Ring

Physical & Mechanical Properties

Outer Diameter (mm): 28.05

Thickness (mm): 0.15

Inner Diameter (mm): 25

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

REACH 241: **Compliant**

Product Details

- Thicknesses Ranging from 0.1mm to 60mm
- Combine Parts of Different Thickness to Create Optimal Spacing
- Dull Black Finish to Reduce Stray Light
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Spacer Rings and Spacer Tubes provide an easy method for controlling optical spacing within **TECHSPEC® Multi-Element Outer Tubes**. Utilizing different combinations of ring and tube thicknesses provides for creating the optimal optical spacing for your application. These spacing elements feature a dull black coating to reduce unwanted internal stray light. TECHSPEC® Multi-Element Spacer Rings and Spacer Tubes are an essential component for any optical system requiring precision spacing of optical elements. Spacer Tubes with a thickness of 10mm or more have an internal baffle thread for a highly anti-reflective effect, further reducing undesired stray light.

Note: The TECHSPEC Spacer Ring Kit ([#11-193](#)) and TECHSPEC Spacer Tube Kit ([#11-208](#)) provide EO's full range of spacing capabilities for a reduced price.

Accessories

	Title		Price	Buy
MORE+	Inner Spacer Ring Kit			5 In Stock <input type="text" value="1"/>
MORE+	Inner Spacer Tube Kit	#11-208	Volume Pricing Request Quote	1 In Stock <input type="text" value="1"/>


Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Related Products



Multi-Element Tube System



Multi-Element Outer Tubes




Multi-Element Tube System Accessories



Multi-Element Inner Single Optic Mounts

Frequently Purchased Together



#02-105 - 12.5mm Diameter Float Glass Window
€15,00



#03-631 - 0.5mm Thick, C-Mount Brass Spacer Ring
€11,25



#32-956 - 6.0mm Dia. x 24.0mm FL, Uncoated, Plano-Convex Lens
€29,50



#53-838 - 111.5mm Length, C-Mount Extension Tube
€96,50

Resources

Media Type

Glossary

GLOSSARY
Bezel

GLOSSARY
Normal Load Capacity

GLOSSARY
Roll

GLOSSARY

GLOSSARY

Yaw

C-Mount

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: