

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

## Basler ace2 GigE/5GigE Cameras



- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace GigE Cameras](#) Also Available

### Common Specifications

#### General

<b>Manufacturer:</b>	Basler	<b>Camera Family:</b>	ace2
----------------------	--------	-----------------------	------

#### Physical & Mechanical Properties

<b>Dimensions (mm):</b>	55.5 x 29 x 29 (excludes connectors and lens mount)	<b>Housing:</b>	Full
-------------------------	---	-----------------	------

#### Sensor

<b>Image Buffer:</b>	Not Specified	<b>Type of Sensor:</b>	Progressive Scan CMOS
<b>Pixel Depth:</b>	8/10/12 bit	<b>Exposure Time:</b>	Freely Programmable

#### Hardware & Interface Connectivity

<b>GPIOs:</b>	1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	<b>Synchronization:</b>	Hardware Trigger (GPIO), Software Trigger, or Free-Run
<b>Interface Port Orientation:</b>	Back Panel	<b>GPIO Connector Type:</b>	6-pin M8


#### Threading & Mounting

<b>Mounting Threads:</b>	1/4-20 with Tripod Mount Adapter <a href="#">#16-641</a>	<b>Mount:</b>	C-Mount
--------------------------	--	---------------	---------


#### Environmental & Durability Factors

<b>Storage Temperature (°C):</b>	-20 to +80
----------------------------------	------------


Technical Information




IMX676 Sensor QE Curve




IMX900 Sensor QE Curve




GMAX2505 Sensor QE Curve




**IMX546 Sensor QE Curve**




**IMX545 Sensor QE Curve**




**GMAX2509 Sensor QE Curve**



**GMAX2518 Sensor QE Curve**



**IMX547 Sensor QE Curve**



**E2525A Sensor QE Curve**

Products

Type	Model Number	Camera Sensor Format	Resolution (MegaPixels)	Connector	Mount	Stock Number	Price	Buy
Color Camera	a2A1920-51gcBAS	1/2.3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-594</a>	€391,00	3-4 days
Monochrome Camera	a2A1920-51gmBAS	1/2.3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-593</a>	€370,00	3-4 days



Recertified

Stock No.: 16-593-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

Recertified  
Products

*Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.*

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold  
as new for the following reasons:

- Open Box – Missing original  
packaging
- Cosmetic Blemishes –  
Scratches, rub marks or other  
minor cosmetic imperfections
- Service/Repair – Product has  
been serviced to the factory  
original specification
- Factory Returns – Product has  
been returned in its original  
condition

Recertified products are inspected for  
damage and any necessary repairs are  
made. Products are then certified by  
Edmund Optics® to be in good working  
order. Since quantity is low, recertified  
products are sold on a first come, first  
serve basis. Any imperfections will be  
listed in the description, indicated in the  
stock number, and categorized by the  
table below. When purchasing  
recertified products, the Edmund  
Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the  
Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

Monochrome Camera    a2A1920-51gmBAS    1/2.3"    2.30    GigE, RJ45 with Screw Locks    C-Mount

3-4 days

Color Camera	a2A1920-51gcPRO	1/2.3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-606</a>	€515,00	3-4 days
--------------	-----------------	--------	------	-----------------------------	---------	-------------------------	---------	----------

Monochrome Camera	a2A1920-51gmPRO	1/2.3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-605</a>	€494,00	Contact Us
Color Camera	a2A1920-165g5cBAS	1/2.3"	2.30	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#25-348</a>	€810,00	3-4 days
Monochrome Camera	a2A1920-165g5mBAS	1/2.3"	2.30	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#25-349</a>	€780,00	3-4 days
Color Camera	a2A2448-105g5cBAS	1/1.8"	5.00	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-600</a>	€1.235,00	3-4 days
Monochrome Camera	a2A2448-105g5mBAS	1/1.8"	5.00	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-599</a>	€1.215,00	3-4 days
Color Camera	a2A2590-22gcBAS	1/2.8"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-596</a>	€329,00	3-4 days
Monochrome Camera	a2A2590-22gmBAS	1/2.8"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-595</a>	€308,00	3-4 days
Color Camera	a2A2590-22gcPRO	1/2.8"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-608</a>	€432,00	Contact Us
Monochrome Camera	a2A2590-22gmPRO	1/2.8"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-607</a>	€411,00	3-4 days
Color Camera	a2A2840-67g5cBAS	2/3"	8.00	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-598</a>	€1.565,00	3-4 days
Monochrome Camera	a2A2840-67g5mBAS	2/3"	8.00	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-597</a>	€1.545,00	3-4 days
Color Camera	a2A3840-13gcBAS	1/1.8"	8.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-598</a>	€370,00	3-4 days
Monochrome Camera	a2A3840-13gmBAS	1/1.8"	8.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-597</a>	€350,00	In Stock
Color Camera	a2A3840-13gcPRO	1/1.8"	8.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-610</a>	€484,00	Contact Us
Monochrome Camera	a2A3840-13gmPRO	1/1.8"	8.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#16-609</a>	€463,00	Contact Us
Color Camera	a2A4096-44g5cBAS	1/1.1"	12.30	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-596</a>	€2.150,00	3-4 days
Monochrome Camera	a2A4096-44g5mBAS	1/1.1"	12.30	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-595</a>	€2.130,00	3-4 days



Recertified

Stock No.: 28-595-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

Recertified  
Products

Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold  
as new for the following reasons:

- Open Box – Missing original  
packaging
- Cosmetic Blemishes –  
Scratches, rub marks or other  
minor cosmetic imperfections
- Service/Repair – Product has  
been serviced to the factory  
original specification
- Factory Returns – Product has  
been returned in its original  
condition

Recertified products are inspected for  
damage and any necessary repairs are  
made. Products are then certified by  
Edmund Optics® to be in good working  
order. Since quantity is low, recertified  
products are sold on a first come, first  
serve basis. Any imperfections will be  
listed in the description, indicated in the  
stock number, and categorized by the  
table below. When purchasing  
recertified products, the Edmund  
Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the  
Web Specials section of our website.

Monochrome Camera	a2A4096- 44g5mBAS	1/1.1"	12.30	5GigE, RJ45 with Screw Locks	C- Mount	€1.550,00	3-4 days
----------------------	----------------------	--------	-------	---------------------------------------	-------------	-----------	----------

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		



Color Camera	a2A4504- 5gcBAS	1.1"	20.20	GigE, RJ45 with Screw Locks	C- Mount	<a href="#">#16-600</a>	€2.030,00	3-4 days
Monochrome Camera	a2A4504- 5gmBAS	1.1"	20.20	GigE, RJ45 with Screw Locks	C- Mount	<a href="#">#16-599</a>	€2.000,00	3-4 days
Color Camera	a2A4504- 5gcPRO	1.1"	20.20	GigE, RJ45 with Screw Locks	C- Mount	<a href="#">#16-612</a>	€2.235,00	Contact Us
Monochrome Camera	a2A4504- 5gmPRO	1.1"	20.20	GigE, RJ45 with Screw Locks	C- Mount	<a href="#">#16-611</a>	€2.215,00	Contact Us

#28-604-RCD-05P Recertified



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 8LJ, UK  
Phone: 1-800-363-1992 : [www.edmundoptics.com](http://www.edmundoptics.com)



Recertified

Stock No.: 28-604-RCD-05P

Recertification Code: 05P (All Original Parts Included, Perfect)

## Recertified Products

Typically 1-2 Recertified Products are in stock at a time. Please contact our sales team if you would like exact availability of an item.

Recertified products are those identified with the recertified logo indicating they were returned to Edmund Optics® and cannot be sold as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

3-4 days

Color Camera	a2A4504-27g5cBAS	1.1"	20.20	5GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#28-604</a>	€2.740,00	Contact Us
--------------	------------------	------	-------	------------------------------	---------	-------------------------	-----------	------------