


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Polished](#)

TECHSPEC® Truncated Precision Aspheric Lenses





- Rectangular and Square Aspheres in 5 x 5mm to 12.5 x 25mm sizes
- Precision Grade Aspheric Figure Error
- Ideal for Integration into Space Sensitive Laser Systems

Common Specifications

Physical & Mechanical Properties

Bevel: Protective bevel as needed	Shape of Back Surface: Plano
Optical Properties	
Asphere Figure Error, RMS @ 632.8nm: 0.4λ	Coating: Uncoated
Surface Quality: 40-20	Conjugate Distance: Infinite

Technical Information



Products

Dimensions (mm)	NA	EFL (mm)	BFL (mm)	CT (mm)	Substrate	Stock Number	Price	Buy
#17-303 Clearance								
<div><div></div><div>×</div></div> <div>Clearance</div> <div>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</div>								
5.00 x 10.00	0.50	10.00	5.68	7.80	N-SF6		€158,00	3-4 days
10.00 x 15.00	0.50	15.00	10.22	8.62	N-SF6	#17-307	€270,00 Qty 6+ €216,00	3-4 days
10.00 x 10.00	0.33	15.00	10.22	8.62	N-SF6	#17-308	€286,00 Qty 6+ €229,00	3-4 days
10.00 x 15.00	0.66	11.25	5.71	10.02	N-SF6	#17-309	€286,00 Qty 6+ €229,00	3-4 days
10.00 x 10.00	0.44	11.25	5.71	10.02	N-SF6	#17-310	€281,00 Qty 6+ €225,00	3-4 days
12.50 x 25.00	0.25	50.00	45.23	7.24	N-BK7	#17-311	€338,00 Qty 6+ €270,00	3-4 days
12.50 x 12.50	0.13	50.00	45.23	7.24	N-BK7	#17-312	€338,00 Qty 6+ €270,00	3-4 days

[#17-313 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

€338,00
Qty 6+ €270,00

3-4 days

12.50 x 25.00 0.33 37.50 31.09 9.72 [N-BK7](#)

[#17-314 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

€338,00
Qty 6+ €270,00

3-4 days

12.50 x 12.50 0.17 37.50 31.09 9.72 [N-BK7](#)

[#17-316 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

12.50 x 12.50 0.20 31.25 23.67 11.50 [N-BK7](#)

€238,00

3-4 days

