

[All Products](#) / [Cameras](#) / [USB Cameras](#)

Pixelink® M-Series Microscopy Cameras



- High Resolution Sensors up to 20 MegaPixel
- Pixelink® Capture Software Included
- Compact Form Factor
- Optional Three-Tier μ Scope Microscopy Software

Common Specifications

General			
Manufacturer: Pixelink		Camera Family: M-Series	
Physical & Mechanical Properties			
Weight (g): 218.5		Housing: Full	
Sensor			
Image Buffer: Not Specified		Type of Sensor: Progressive Scan CMOS	
Exposure Time: Not Specified		Machine Vision Standard: USB3 Vision	
Electrical			
Power Consumption (W):		Not Specified	
Hardware & Interface Connectivity			
Video Output: USB 3.0			
Connector: USB 3.0, Micro-B		Power Supply: Power over USB	
GPIOs: None		Synchronization: Software Trigger	
Interface Port Orientation: Back Panel		GPIO Connector Type: None	
Threading & Mounting			
Mounting Threads: No Mounting Threads/Tripod Adapter		Mount: C-Mount	
Environmental & Durability Factors			
Operating Temperature (°C): 0 to +50		Storage Temperature (°C): -45 to +85	

Technical Information

Products

Type	Model Number	Camera Sensor Format	Resolution (MegaPixels)	Connector	Mount	Stock Number	Price	Buy
Monochrome Microscopy Camera	M1M-CYL	1/2"	1.30	USB 3.0, Micro-B	C-Mount	#17-814	€1.040,00	Contact Us
Color Microscopy Camera	M1C-CYL	1/2"	1.30	USB 3.0, Micro-B	C-Mount	#17-813	€1.040,00	Contact Us
Monochrome Microscopy Camera	M2M-CYL	2/3"	2.20	USB 3.0, Micro-B	C-Mount	#17-818	€1.345,00	In Stock
Color Microscopy Camera	M2C-CYL	2/3"	2.20	USB 3.0, Micro-B	C-Mount	#17-817	€1.970,00	In Stock
Monochrome Microscopy Camera	M4M-CYL	1"	4.20	USB 3.0, Micro-B	C-Mount	#17-820	€2.285,00	Contact Us
Color Microscopy Camera	M4C-CYL	1"	4.20	USB 3.0, Micro-B	C-Mount	#17-819	€1.820,00	In Stock
Monochrome Microscopy Camera	M5DM-CYL	2/3"	5.00	USB 3.0, Micro-B	C-Mount	#17-824	€2.075,00	In Stock
Color Microscopy Camera	M5DC-CYL	2/3"	5.00	USB 3.0, Micro-B	C-Mount	#17-823	€2.075,00	In Stock
#17-821 Clearance								
<div><div><div>×</div></div><div>Clearance</div><div>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</div></div>								
Microscopy Camera	M5C-CYL	1"	5.30	USB 3.0, Micro-B	C-Mount		€1.660,00	3-4 days
Monochrome Microscopy Camera	M9M-CYL	1"	8.85	USB 3.0, Micro-B	C-Mount	#17-826	€2.600,00	Contact Us

Color Microscopy Camera	M9C-CYL	1"	8.85	USB 3.0, Micro-B	C-Mount	#17-825	€2.600,00	Contact Us
Monochrome Microscopy Camera	M12BM-CYL	1.1"	12.30	USB 3.0, Micro-B	C-Mount	#17-810	€3.010,00	In Stock
Monochrome Microscopy Camera	M12M-CYL	1.1"	12.30	USB 3.0, Micro-B	C-Mount	#17-812	€3.635,00	In Stock
Color Microscopy Camera	M12BC-CYL	1.1"	12.30	USB 3.0, Micro-B	C-Mount	#17-809	€3.010,00	In Stock
Color Microscopy Camera	M12C-CYL	1.1"	12.30	USB 3.0, Micro-B	C-Mount	#17-811	€3.635,00	In Stock
Color Microscopy Camera	M18C-CYL	1/2.3"	18.00	USB 3.0, Micro-B	C-Mount	#21-072	€1.450,00	In Stock
Monochrome Microscopy Camera	M20M-CYL	1"	20.00	USB 3.0, Micro-B	C-Mount	#17-816	€1.450,00	In Stock
Color Microscopy Camera	M20C-CYL	1"	20.00	USB 3.0, Micro-B	C-Mount	#17-815	€1.450,00	In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com