

[All Products](#) / [Optics](#) / [Prisms](#) / [Dispersion Prisms](#)

ISP Optics Infrared (IR) Equilateral Prisms

See More by [ISP Optics](#)



- CaF<sub>2</sub>, Ge, and ZnSe Substrates
- Ideal for Wavelength Separation
- Designed for Use with Collimated Sources
- Additional [Infrared Optics](#) Available
- Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).

Common Specifications



Physical & Mechanical Properties

Dimensional Tolerance (mm):	±0.25
-----------------------------	-------


Optical Properties

Coating:	Uncoated
Angle Tolerance (arcmin):	±10

Technical Information



Zinc Selenide



Products

Length of Legs (mm)	Length of Hypotenuse (mm)	Coating	Substrate	Wavelength Range (nm)	Model Number	Stock Number	Price	Buy
<a href="#">#19-709 Clearance</a>								
<div><div></div><div>Clearance</div><div>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</div></div>								
12.70	12.70	Uncoated	<a href="#">Calcium Fluoride (CaF<sub>2</sub>)</a>	200 - 7000	CF-EP-12		€1.450,00 Qty 6+ €1.160,00	3-4 days
<a href="#">#25-038 Clearance</a>								
<div><div></div><div>Clearance</div><div>Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.</div></div>								
25.40	25.40	Uncoated	Barium Fluoride (BaF <sub>2</sub> )	200 - 12000	BF-EP-25		€1.490,00	3-4 days

[#19-710 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.40	25.40	Uncoated	<a href="#">Calcium Fluoride (CaF<sub>2</sub>)</a>	200 - 7000	CF-EP-25	€1.770,00 Qty 6+ €1.415,00	3-4 days
-------	-------	----------	--	------------	----------	-------------------------------	----------

---

[#19-713 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

12.70	12.70	Uncoated	Zinc Selenide (ZnSe)	600 - 18000	GE-EP-12	€1.390,00 Qty 6+ €1.110,00	3-4 days
-------	-------	----------	----------------------	-------------	----------	-------------------------------	----------

---

[#19-714 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.40	25.40	Uncoated	Zinc Selenide (ZnSe)	600 - 18000	GE-EP-25		€2.355,00 Qty 6+ €1.885,00	3-4 days
-------	-------	----------	----------------------	-------------	----------	--	-------------------------------	----------

12.70	12.70	Uncoated	Germanium (Ge)	2000 - 14000	ZC-EP-12	<a href="#">#19-711</a>	€1.450,00 Qty 6+ €1.160,00	3-4 days
-------	-------	----------	----------------	--------------	----------	-------------------------	-------------------------------	----------

25.40	25.40	Uncoated	Germanium (Ge)	2000 - 14000	ZC-EP-25	<a href="#">#19-712</a>	€2.135,00 Qty 6+ €1.710,00	3-4 days
-------	-------	----------	----------------	--------------	----------	-------------------------	-------------------------------	----------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)