


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

Acrylic (PMMA) Plastic Windows



- Highly Scratch-Resistant
- High Visible Light Transmission
- Cost-Effective Alternative to Glass
- [Polycarbonate Plastic Windows](#) Also Available

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed

Edges: Smooth, Machined

Optical Properties

Abbe Number (v_d): 58

Coating: Uncoated

Index of Refraction (n_d): 1.49



Substrate: PMMA

Wavelength Range (nm): 400 - 1600

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$): 60

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
25.40	-	1.52	Uncoated	#19-634	€23,00 Qty 6+ €18,25	In Stock
#71-541 New						
<div><div><div>×</div></div><div>New</div><div>Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!</div></div>						
38.10	-	1.52	Uncoated		€26,00 Qty 6+ €20,75	3-4 days
50.80	-	1.52	Uncoated	#19-635	€28,00 Qty 6+ €22,25	3-4 days

[#71-542 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

63.50	-	1.52	Uncoated		€31,25 Qty 6+ €25,00	3-4 days
-------	---	------	----------	--	-------------------------	----------

-	50.80 x 50.80	1.52	Uncoated	#19-636	€28,00 Qty 6+ €22,25	3-4 days
---	---------------	------	----------	-------------------------	-------------------------	----------

76.20	-	1.52	Uncoated	#19-637	€33,75 Qty 6+ €27,00	3-4 days
-------	---	------	----------	-------------------------	-------------------------	----------

-	76.20 x 76.20	1.52	Uncoated	#19-638	€33,75 Qty 6+ €27,00	3-4 days
---	---------------	------	----------	-------------------------	-------------------------	----------

-	101.6 x 127.0	1.52	Uncoated	#19-639	€44,75 Qty 6+ €36,00	3-4 days
---	---------------	------	----------	-------------------------	-------------------------	----------

[#71-543 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

-	127.00 x 177.80	1.52	Uncoated		€54,50 Qty 6+ €43,50	In Stock
---	--------------------	------	----------	--	-------------------------	----------

-	203.2 x 254.0	1.52	Uncoated	#19-640	€88,50 Qty 6+ €70,50	3-4 days
---	---------------	------	----------	-------------------------	-------------------------	----------

[#71-544 New](#)



New

-	254.00 x 304.80	1.52	Uncoated	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€125,00 Qty 6+ €100,00	3-4 days
---	--------------------	------	----------	--	---------------------------	----------

[#71-545 New](#)



New

-	304.80 x 355.60	1.52	Uncoated	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€140,00 Qty 6+ €112,00	3-4 days
---	--------------------	------	----------	--	---------------------------	----------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com