

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Polymer Film Polarizers](#)

Ultraviolet (UV) Linear Polarizing Film



- High UV Transmission from 325 - 400nm
- 1000:1 Contrast From 325 - 400nm, 6000:1 Contrast From 400 - 750nm
- Thin, Versatile Polymer Substrate

Common Specifications

Physical & Mechanical Properties

Construction: Polarizing Film

Optical Properties

Coating: Uncoated

Extinction Ratio: 1000:1 (avg @ 325nm-400nm)
6000:1 (avg @ 400nm-750nm)

Substrate: CTA (Cellulose Triacetate)

Wavelength Range (nm): 320 - 750

Transmission, Single (%): 39 (325nm-400nm)

Transmission, Crossed (%): 0.04 (325nm-400nm)

Environmental & Durability Factors

Operating Temperature (°C):

Heat Resistance: 70°C dry
Cold Resistance: -20°C

Storage Temperature (°C):

15 - 25

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
#72-678 New					
					
New					
10.00	-	0.19	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€30,00 Qty 10+ €24,00	3-4 days
#72-679 New					
					
New					
12.00	-	0.19	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€34,00 Qty 10+ €27,00	3-4 days
-	12.5 x 12.5	0.19	#25-112	€34,00 Qty 10+ €27,00	3-4 days

[#72-680 New](#)



New

20.00	-	0.19	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€41,00 Qty 10+ €32,00	3-4 days
-------	---	------	--	--------------------------	----------

[#72-681 New](#)



New

25.00	-	0.19	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€48,00 Qty 10+ €38,00	3-4 days
-------	---	------	--	--------------------------	----------

-	25.0 x 25.0	0.19	#25-111	€48,00 Qty 10+ €38,00	3-4 days
---	-------------	------	-------------------------	--------------------------	----------

[#72-682 New](#)



New

50.00	-	0.19	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€123,00 Qty 10+ €98,00	3-4 days
-------	---	------	--	---------------------------	----------

-	50.0 x 50.0	0.19	#25-110	€123,00 Qty 10+ €99,00	3-4 days
-	75.0 x 75.0	0.19	#25-109	€241,00 Qty 10+ €192,00	3-4 days
-	150.0 x 150.0	0.19	#25-108	€745,00 Qty 10+ €596,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com