

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Concave \(DCV\) Lenses](#)

TECHSPEC® VIS-EXT Coated Double-Concave (DCV) Lenses



- AR Coated to Provide <0.5% Reflectance per Surface for 350 - 700nm
- Designed for 0° Angle of Incidence
- Precision Diameter and Centration Tolerances Allow for Easy OEM Integration
- Additional AR Coating Options Available: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

Common Specifications

Physical & Mechanical Properties

Bevel:

Protective bevel as needed


Optical Properties

Substrate:

[N-BK7](#)

Coating:	VIS-EXT (350-700nm)	Wavelength Range (nm):	350 - 700
Coating Specification:	$R_{avg} \leq 0.4\%$ @ 425 - 675nm	Focal Length Specification Wavelength (nm):	587.6
Focal Length Tolerance (%):	± 1	Surface Quality:	40-20
Damage Threshold, By Design:	5 J/cm ² @ 532nm, 10ns	Power (P-V) @ 632.8nm:	1.5W
Irregularity (P-V) @ 632.8nm:	$\lambda/4$		

Technical Information



Products

Title	Stock Number	Price	Buy
6mm Dia. x -9mm FL, VIS-EXT Coated, Double-Concave Lens	#26-668	€42,50 Qty 10+ €38,25	3-4 days
6mm Dia. x -12mm FL, VIS-EXT Coated, Double-Concave Lens	#26-669	€42,50 Qty 10+ €38,25	3-4 days
9mm Dia. x -18mm FL, VIS-EXT Coated, Double-Concave Lens	#26-670	€43,50 Qty 10+ €39,00	3-4 days
12mm Dia. x -18mm FL, VIS-EXT Coated, Double-Concave Lens	#26-671	€47,00 Qty 10+ €42,25	3-4 days
12mm Dia. x -24mm FL, VIS-EXT Coated, Double-Concave Lens	#26-672	€47,00 Qty 10+ €42,25	In Stock
25mm Dia. x -50mm FL, VIS-EXT Coated, Double-Concave Lens	#26-673	€51,50 Qty 10+ €46,25	3-4 days
25mm Dia. x -100mm FL, VIS-EXT Coated, Double-Concave Lens	#26-674	€51,50 Qty 10+ €46,25	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com