


[All Products](#) /
 [Optics](#) /
 [Optical Mirrors](#) /
 [Flat Mirrors](#) /
 [Precision Polished Metal Coatings](#)

TECHSPEC® ZERODUR® Mirror Substrates



- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground
Parallelism (arcsec):	30		

Optical Properties

Coating:	Uncoated		
Surface Flatness (P-V):	$\lambda/10$	Substrate:	ZERODUR®
Surface Quality:	20-10		

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
5.00	-	2.00	#71-503	€72,10	1 In Stock
-	5 x 5	2.00	#71-504	€72,10	1 In Stock
12.50	-	3.00	#71-507	€74,68	1 In Stock
-	12.5 x 12.5	3.00	#71-508	€74,68	1 In Stock
25.40	-	6.35	#71-515	€108,15	Contact Us
30.00	-	5.00	#71-516	€118,45	Contact Us
-	30.0 x 30.0	5.00	#71-517	€118,45	1 In Stock
40.00	-	5.00	#71-518	€123,60	1 In Stock
-	40.0 x 40.0	5.00	#71-519	€123,60	1 In Stock
75.00	-	7.50	#71-522	€365,65	4 In Stock
-	75.0 x 75.0	7.50	#71-523	€365,65	Contact Us
100.00	-	10.00	#71-524	€428,48	1 In Stock
-	100.0 x 100.0	10.00	#71-525	€428,48	1 In Stock
10.00	-	2.00	#71-505	€72,10	Contact Us
-	10.0 x 10.0	2.00	#71-506	€72,10	1 In Stock
15.00	-	3.00	#71-509	€77,77	1 In Stock
-	15.0 x 15.0	3.00	#71-510	€77,77	1 In Stock
20.00	-	3.00	#71-511	€83,43	2 In Stock
-	20.0 x 20.0	3.00	#71-512	€83,43	1 In Stock
25.00	-	4.00	#71-513	€91,67	1 In Stock
-	25.0 x 25.0	4.00	#71-514	€91,67	1 In Stock
50.00	-	5.00	#71-520	€164,80	2 In Stock
-	50.0 x 50.0	5.00	#71-521	€164,80	1 In Stock



Copyright 2025 | Edmund Optics BV, De Maas 22B, 5684 PL Best, The Netherlands

Phone: 1-800-363-1992 :

www.edmundoptics.com